

## Base strip - MSTBVA 2,5/ 3-G YE - 1710639

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Header, Nominal current: 12 A, Rated voltage (III/2): 320 V, Number of positions: 3, Pitch: 5 mm, Color: yellow, Contact surface: Tin, Mounting: Wave soldering



The figure shows a 10-position version of the product



### Key Commercial Data

Packing unit	1 STK
Minimum order quantity	100 STK
GTIN	 4 055626 195841
GTIN	4055626195841
Weight per Piece (excluding packing)	0.010 g
Custom tariff number	85366990
Country of origin	Germany

### Technical data

#### Dimensions

Length	8.6 mm
Pitch	5 mm
Dimension a	10 mm
Width	17 mm
Constructional height	12 mm
Height	15.9 mm
Length of the solder pin	3.9 mm
Pin dimensions	1 x 1 mm
Hole diameter	1.4 mm

## Base strip - MSTBVA 2,5/ 3-G YE - 1710639

### Technical data

#### General

Insulating material group	I
Rated voltage (III/2)	320 V
Nominal current I <sub>N</sub>	12 A
Flammability rating according to UL 94	V0
Color	yellow
Number of positions	3

#### Standards and Regulations

Flammability rating according to UL 94	V0
--	----

#### Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

### Classifications

#### eCl@ss

eCl@ss 8.0	27440402
eCl@ss 9.0	27440402

#### ETIM

ETIM 5.0	EC002637
ETIM 6.0	EC002637

#### UNSPSC

UNSPSC 13.2	39121409
-------------	----------