

Cable marker carrier - GKM 1 GY - 1750498

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cable marker carrier, gray, unlabeled, Mounting type: clip on, Cable diameter: 0-2.5 mm, Lettering field: 20 mm x 8 mm

Product Features

- SS-ZB ..., UC-TM ... or ZB ... can be used for labeling purposes
- The conductor marker is attached directly to a conductor

Key Commercial Data

Packing unit	1 pc
GTIN	 4 017918 028299
Weight per Piece (excluding packing)	2.22 g
Custom tariff number	39269097
Country of origin	Germany

Technical data

Dimensions

Width (a)	20 mm
Cable diameter	0 mm ... 2.5 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 80 °C
---------------------------------	------------------

General

Color	gray
Components	free from silicone and halogen
Flammability rating according to UL 94	V2
Material	PA/ABS
Marking mounting type	clip on

Standards and Regulations

Cable marker carrier - GKM 1 GY - 1750498

Technical data

Standards and Regulations

Flammability rating according to UL 94	V2
--	----

Classifications

eCl@ss

eCl@ss 4.0	24190219
eCl@ss 4.1	24190219
eCl@ss 5.0	27149103
eCl@ss 5.1	27400401
eCl@ss 6.0	27400401
eCl@ss 7.0	27400401
eCl@ss 8.0	27400401
eCl@ss 9.0	27400401

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC001530

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410