

Plug - STB 3/4-ST-5,08 - 1752043

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Plug component, Number of positions: 4, Pitch: 5.08 mm, Connection method: Screw connection with tension sleeve, Color: green, Contact surface: Tin



Key Commercial Data

Packing unit	1 pc
GTIN	 4 017918 028367
Weight per Piece (excluding packing)	11.71 g
Custom tariff number	85369010
Country of origin	Poland

Technical data

Dimensions

Pitch	5.08 mm
-------	---------

General

Range of articles	STB
Type of contact	Female connector
Number of positions	4
Connection method	Screw connection with tension sleeve
Nominal cross section	2.5 mm ²
Stripping length	8 mm
Screw thread	M3

Connection data

Minimum AWG according to UL/CUL	30
Maximum AWG according to UL/CUL	14

Standards and Regulations

Connection in acc. with standard	CSA
----------------------------------	-----

Plug - STB 3/4-ST-5,08 - 1752043

Classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260704
eCl@ss 7.0	27440490
eCl@ss 8.0	27440309
eCl@ss 9.0	27440309

ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC002498
ETIM 5.0	EC002638

UNSPSC

UNSPSC 6.01	30211810
UNSPSC 7.0901	39121409
UNSPSC 11	39121409
UNSPSC 12.01	39121409
UNSPSC 13.2	39121409

Approvals

Approvals

Approvals

CSA / UL Recognized / EAC / EAC


Ex Approvals


Approvals submitted

Approval details

Plug - STB 3/4-ST-5,08 - 1752043

Approvals

CSA 	
mm ² /AWG/kcmil	28-14
Nominal current I _N	10 A
Nominal voltage U _N	300 V

UL Recognized 	
mm ² /AWG/kcmil	30-14
Nominal current I _N	10 A
Nominal voltage U _N	300 V

EAC

EAC
