

Protective covers - HC-B 16-SD-FQ/FS - 1772599


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



HEAVYCON protective cover, series B16, for supporting base element with double locking latch, with retaining cord, IP54, PA



Key Commercial Data

Packing unit	1 pc
Minimum order quantity	10 pc
GTIN	 4 017918 037260
Weight per Piece (excluding packing)	34.12 g
Custom tariff number	85389099
Country of origin	Germany

Technical data

Dimensions

Diameter of retaining cord eyelet	30 mm
-----------------------------------	-------

Ambient conditions

Degree of protection	IP54
Ambient temperature (operation)	-20 °C ... 100 °C

General

Type	B16
	For supporting base element with double locking latch
Material	PA
Flammability rating according to UL 94	HB
Seal present	no
Assembly instructions	Not for HC-B...EMC housings

Protective covers - HC-B 16-SD-FQ/FS - 1772599

Technical data

General

Connection	Plastic protective cover for short-term protection
------------	--

Standards and Regulations

Flammability rating according to UL 94	HB
--	----

Classifications

eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816
eCl@ss 5.0	27142104
eCl@ss 5.1	27142104
eCl@ss 6.0	27142104
eCl@ss 7.0	27142104
eCl@ss 8.0	27440208
eCl@ss 9.0	27440208

ETIM

ETIM 2.0	EC000437
ETIM 3.0	EC000437
ETIM 4.0	EC000437
ETIM 5.0	EC002314

UNSPSC

UNSPSC 6.01	30212113
UNSPSC 7.0901	39121712
UNSPSC 11	39121712
UNSPSC 12.01	39121712
UNSPSC 13.2	39121712

Approvals

Approvals

Approvals

EAC

Protective covers - HC-B 16-SD-FQ/FS - 1772599

Approvals

Ex Approvals


Approvals submitted

Approval details

EAC

Drawings

Dimensional drawing



Protective cover, B16
