

## Cable housing - KGG-PC 4/ 5 - 1837243

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cable housing, Pitch: 0 mm, Number of positions: 5, Dimension a: 39.9 mm, Color: green

### Product Features

- Ergonomic cable housing for standard PC 4 plugs with screw connection
- A cable clamp can be mounted back to front



### Key Commercial Data

Packing unit	1 pc
Minimum order quantity	10 pc
GTIN	 4 017918 111281
Weight per Piece (excluding packing)	18.6 g
Custom tariff number	85389099
Country of origin	Poland

### Technical data

#### Dimensions

Pitch	0.00 mm
Dimension a	39.9 mm

#### General

Range of articles	KGG-PC 4
Insulating material group	0
Insulating material	ABS
Flammability rating according to UL 94	HB
Number of positions	5

# Cable housing - KGG-PC 4/ 5 - 1837243

## Technical data

### Standards and Regulations

Flammability rating according to UL 94	HB
--	----

## Classifications

### eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260704
eCl@ss 7.0	27440402
eCl@ss 8.0	27440202
eCl@ss 9.0	27440202

### ETIM

ETIM 3.0	EC000058
ETIM 4.0	EC000437
ETIM 5.0	EC000437

### UNSPSC

UNSPSC 6.01	30211810
UNSPSC 7.0901	39121409
UNSPSC 11	39121409
UNSPSC 12.01	39121409
UNSPSC 13.2	39121409

## Approvals

### Approvals

---

Approvals

EAC / EAC

---

Ex Approvals

---

Approvals submitted

## Cable housing - KGG-PC 4/ 5 - 1837243

### Approvals

---

#### Approval details

EAC

EAC

### Drawings

Dimensional drawing

