

Cable housing - KGS-PC 4/ 7 - 1837269

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cable housing, Pitch: 0 mm, Number of positions: 7, Dimension a: 55.14 mm, Color: green

Product Features

- ✓ Ergonomic cable housing for standard PC 4 plugs with screw connection
- ✓ KGG-PC 4 for cable diameters from 4 to 13.5 mm²
- ✓ KGS-PC 4 (angled cable outlet) for cable diameters from 6 to 16 mm²
- ✓ A cable clamp can be mounted back to front



Key Commercial Data

Packing unit	1 pc
Minimum order quantity	10 pc
Weight per Piece (excluding packing)	27.36 g
Custom tariff number	85389099
Country of origin	Poland

Technical data

Dimensions

Pitch	0.00 mm
Dimension a	55.14 mm

General

Range of articles	KGS-PC 4
Insulating material group	0
Insulating material	ABS
Flammability rating according to UL 94	HB
Number of positions	7

Standards and Regulations

Cable housing - KGS-PC 4/ 7 - 1837269

Technical data

Standards and Regulations

Flammability rating according to UL 94	HB
--	----

Classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260704
eCl@ss 7.0	27440402
eCl@ss 8.0	27440202
eCl@ss 9.0	27440202

ETIM

ETIM 3.0	EC000058
ETIM 4.0	EC000437
ETIM 5.0	EC000437

UNSPSC

UNSPSC 6.01	30211810
UNSPSC 7.0901	39121409
UNSPSC 11	39121409
UNSPSC 12.01	39121409
UNSPSC 13.2	39121409

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approvals submitted

Cable housing - KGS-PC 4/ 7 - 1837269

Approvals

Approval details

EAC

Drawings

Dimensional drawing

