

## Half screw connection - VC-M-KV-PG21(11,5-15,5) - 1854035

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Half screw connection Pg21, made of metal, consisting of rubber seal with one hole and one pressure screw, for type 2 - 4 housings, cable [mm] 11.5 - 13.5

### Key Commercial Data

Packing unit	1 pc
Minimum order quantity	5 pc
GTIN	 4 017918 145941
Weight per Piece (excluding packing)	33.8 g
Custom tariff number	74153300
Country of origin	Poland

### Technical data

#### Dimensions

Wrench size, union nut	30 mm
External cable diameter	11.5 mm ... 15.5 mm

#### Ambient conditions

Degree of protection	IP67
Ambient temperature (operation)	-40 °C ... 125 °C

#### General

Note	Adapter screw connections are available on request for large cable dimensions, from Pg16 to Pg21 and from Pg21 to Pg29
Material, pressure screw	Nickel-plated brass
Seal material	TPE
Cable seal material	TPE
Shielded	No
Thread type on seal side	Pg21

# Half screw connection - VC-M-KV-PG21(11,5-15,5) - 1854035

## Technical data

### General

Tightening torque, union nut	10.00 Nm
------------------------------	----------

## Classifications

### eCl@ss

eCl@ss 4.0	27141209
eCl@ss 4.1	27141209
eCl@ss 5.0	27149109
eCl@ss 5.1	27149109
eCl@ss 6.0	27149109
eCl@ss 7.0	27149109

### ETIM

ETIM 2.0	EC000441
ETIM 3.0	EC000441
ETIM 4.0	EC000441
ETIM 5.0	EC000441

### UNSPSC

UNSPSC 6.01	31261502
UNSPSC 7.0901	31261502
UNSPSC 11	31261502
UNSPSC 12.01	31261502
UNSPSC 13.2	31261502

## Approvals

### Approvals

---

#### Approvals

EAC

---

#### Ex Approvals

---

#### Approvals submitted

---

## Half screw connection - VC-M-KV-PG21(11,5-15,5) - 1854035

### Approvals

#### Approval details

EAC
-----