

Cable gland - VC-K-KV-PG16(11,5-15,5) - 1854844

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Half screw connection Pg16, made of plastic, consisting of rubber seal with one hole and one pressure screw, for type 1 housings, cable [mm] 11.5 - 15.5

Key Commercial Data

Packing unit	1 pc
Minimum order quantity	5 pc
GTIN	 4 017918 146054
Weight per Piece (excluding packing)	6.37 g
Custom tariff number	39269097
Country of origin	Poland

Technical data

Dimensions

Wrench size, union nut	27 mm
External cable diameter	11.5 mm ... 15.5 mm

Ambient conditions

Degree of protection	IP67
	IP66 (for housings HC-COM-K...)
	IP65 (for housings HC-COM-K...)
Ambient temperature (operation)	-20 °C ... 100 °C

General

Note	Adapter screw connections are available on request for large cable dimensions, from Pg16 to Pg21 and from Pg21 to Pg29
Type of the screw connection	Half screw connection
Material, pressure screw	Polyamide
Seal material	TPE
Shielded	No

Cable gland - VC-K-KV-PG16(11,5-15,5) - 1854844

Technical data

General

Thread type on seal side	Pg16
Tightening torque, union nut	5.00 Nm

Classifications

eCl@ss

eCl@ss 4.0	27141209
eCl@ss 4.1	27141209
eCl@ss 5.0	27149109
eCl@ss 5.1	27149109
eCl@ss 6.0	27149109
eCl@ss 7.0	27149109
eCl@ss 8.0	27149109

ETIM

ETIM 2.0	EC000441
ETIM 3.0	EC000441
ETIM 4.0	EC000441
ETIM 5.0	EC000441

UNSPSC

UNSPSC 6.01	31261502
UNSPSC 7.0901	31261502
UNSPSC 11	31261502
UNSPSC 12.01	31261502
UNSPSC 13.2	31261502

Approvals

Approvals

Approvals

EAC

Ex Approvals

Cable gland - VC-K-KV-PG16(11,5-15,5) - 1854844

Approvals

Approvals submitted

Approval details

EAC
