

## Housing - VC-MEMV-T2-R - 1855144

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Metal sleeve housing, EMC-coating, locking screws with knurled head, with conductive seal, type 2, cable screw connection Pg21

The illustration shows version VC-MEMV-T3-R



### Key Commercial Data

Packing unit	1 pc
Weight per Piece (excluding packing)	288.64 g
Custom tariff number	85389099
Country of origin	Poland

### Technical data

#### Dimensions

Height	65 mm
Width	33 mm
Length	74 m

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

#### General

Note	When using fiber optics, the bending radii of the cable manufacturers must be observed.
Size	VC2
Color	nickel
Locking type	Screw locking, knurled head
Tightening torque, mounting screw	1 Nm ±0.5 Nm
No. of cable outlets	1
Cable exit	Angled

# Housing - VC-MEMV-T2-R - 1855144

## Technical data

### General

Screw connection	none
Type of the screw connection	Pg21
Housing material	Zinc die-cast, surface bronzed and nickel-plated
Housing surface material	Nickel-plated
Seal material	EPDM, conductive
Material of locking screw	Nickel-plated brass

## Classifications

### eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816
eCl@ss 5.0	27371205
eCl@ss 5.1	27371205
eCl@ss 6.0	27371205
eCl@ss 7.0	27371205
eCl@ss 8.0	27440202
eCl@ss 9.0	27440202

### ETIM

ETIM 2.0	EC000437
ETIM 3.0	EC000437
ETIM 4.0	EC000437
ETIM 5.0	EC000437

### UNSPSC

UNSPSC 6.01	31261502
UNSPSC 7.0901	31261502
UNSPSC 11	31261502
UNSPSC 12.01	31261502
UNSPSC 13.2	31261502

## Approvals

### Approvals

---

Approvals

EAC

# Housing - VC-MEMV-T2-R - 1855144

## Approvals

---

Ex Approvals

---

Approvals submitted

---

Approval details

EAC
-----

## Drawings

Dimensional drawing

