

Adapter plate - HC-B 24-ADP-VC-4 - 1885842


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Adapter plates 2 mm thick, for panel cutouts of HC-B 24 size, including 1.5 mm flat gasket, size 4



Key Commercial Data

Packing unit	1 pc
Minimum order quantity	5 pc
GTIN	 4 017918 178598
GTIN	4017918178598
Weight per Piece (excluding packing)	74.500 g
Custom tariff number	85472000
Country of origin	Germany

Technical data

Dimensions

Length	3.5 mm
Height	43 mm
Width	141 mm

General

Material	V2A
Type	VC4

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
------------	---

Adapter plate - HC-B 24-ADP-VC-4 - 1885842

Technical data

Environmental Product Compliance

	No hazardous substances above threshold values
--	--

Classifications

eCl@ss

eCl@ss 4.0	27140815
eCl@ss 4.1	27140815
eCl@ss 5.0	27143423
eCl@ss 5.1	27143400
eCl@ss 6.0	27261200
eCl@ss 7.0	27440201
eCl@ss 8.0	27440201
eCl@ss 9.0	27440201

ETIM

ETIM 2.0	EC000201
ETIM 3.0	EC000201
ETIM 4.0	EC000201
ETIM 5.0	EC002309
ETIM 6.0	EC002309

UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	39121421