


Printed-circuit board connector - MSTBA 2,5/ 4-G THT-R32 - 1970087

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

PCB headers, number of positions: 4, pitch: 5 mm, color: black



Key Commercial Data

Packing unit	1 pc
Minimum order quantity	330 pc
GTIN	 4 017918 929749
GTIN	4017918929749
Weight per Piece (excluding packing)	3.440 g
Custom tariff number	85366930
Country of origin	Germany

Technical data

Dimensions

Pitch	5 mm
Dimension a	15 mm
Height	9 mm
Length of the solder pin	2.9 mm

General

Range of articles	MSTBA 2,5/..-G-THT
Rated voltage (III/3)	250 V
Connection in acc. with standard	EN-VDE
Nominal current I _N	12 A
Color	black
Number of positions	4

Standards and Regulations

Connection in acc. with standard	EN-VDE
	CUL

Printed-circuit board connector - MSTBA 2,5/ 4-G THT-R32 - 1970087

Technical data

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260700
eCl@ss 6.0	27260700
eCl@ss 7.0	27440402
eCl@ss 8.0	27440402
eCl@ss 9.0	27440402

ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC002637
ETIM 5.0	EC002637
ETIM 6.0	EC002637

UNSPSC

UNSPSC 6.01	30211810
UNSPSC 7.0901	39121409
UNSPSC 11	39121409
UNSPSC 12.01	39121409
UNSPSC 13.2	39121409