


## Side element - UM108 N-SE-A73 BK - 2200092

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Side element, without foot, low-profile version, for 73 mm wide U-shaped cover.



### Key Commercial Data

Packing unit	1 pc
Minimum order quantity	250 pc
GTIN	 4 046356 511674
GTIN	4046356511674
Weight per Piece (excluding packing)	12.000 g
Custom tariff number	39269097
Country of origin	Germany

### Technical data

#### Product properties

Brief article description	Side element
Type	UM108 N-SE-A73 BK
Order No.	2200092
Housing type	Press-drawn section housings
Type	Lateral element

#### Material specifications

Housing material	Polyamide
Color (RAL)	black
Flammability rating according to UL 94	V0

## Side element - UM108 N-SE-A73 BK - 2200092

### Technical data

#### Packaging specifications

Pieces per package	10
Denomination packing units	Pcs.

#### Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

### Classifications

#### eCl@ss

eCl@ss 10.0.1	27182701
eCl@ss 11.0	27182701
eCl@ss 4.0	27180400
eCl@ss 4.1	27180400
eCl@ss 5.0	27180500
eCl@ss 5.1	27180500
eCl@ss 6.0	27180800
eCl@ss 7.0	27182701
eCl@ss 9.0	27182701

#### ETIM

ETIM 3.0	EC001031
ETIM 4.0	EC001031
ETIM 6.0	EC002779
ETIM 7.0	EC002779

#### UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501
UNSPSC 18.0	31261501
UNSPSC 19.0	31261501
UNSPSC 20.0	31261501
UNSPSC 21.0	31261501

## Side element - UM108 N-SE-A73 BK - 2200092

### Approvals

Approvals

---

Approvals

UL Recognized

---

Ex Approvals

---

### Approval details

UL Recognized



<http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm>

FILE E 240868