

Side element - UM-PRO 108 COVER-R BK - 2200156

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Lateral element (right) with mounting foot for DIN rails UM-PRO profiles for PCB width of 108 mm



Your advantages

- ✔ Item is from the UM-BASIC/UM-PRO product range
- ✔ PVC press-drawn section (UM-BASIC) or PA (UM-PRO)
- ✔ Available in individual lengths
- ✔ Available in the overall widths of 72 mm, 108 mm, and 122 mm
- ✔ Variety of connection technologies
- ✔ Can be mounted on the DIN rail

Key Commercial Data

Packing unit	1 pc
Minimum order quantity	10 pc
GTIN	 4 046356 547383
GTIN	4046356547383
Weight per Piece (excluding packing)	18.000 g
Custom tariff number	39269097
Country of origin	Germany

Technical data

General

Housing type	Press-drawn section housings
Housing material	Polyamide
Color (RAL)	black

Side element - UM-PRO 108 COVER-R BK - 2200156

Technical data

Ambient conditions

Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
---------------------------------	--

Dimensions

Length	15.5 mm
Height	40 mm
Width	127.8 mm

Standards and Regulations

Flammability rating according to UL 94	V0
--	----

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 10.0.1	27182701
eCl@ss 4.0	27180400
eCl@ss 4.1	27180400
eCl@ss 5.0	27180500
eCl@ss 5.1	27180500
eCl@ss 6.0	27182000
eCl@ss 7.0	27182701
eCl@ss 8.0	27182701
eCl@ss 9.0	27182701

ETIM

ETIM 2.0	EC001031
ETIM 3.0	EC001031
ETIM 4.0	EC000721
ETIM 5.0	EC002779
ETIM 6.0	EC002779
ETIM 7.0	EC002779

UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501

Side element - UM-PRO 108 COVER-R BK - 2200156

Classifications

UNSPSC

UNSPSC 12.01	31261501
UNSPSC 13.2	31261501

Approvals

Approvals


Approvals

UL Recognized / EAC

Ex Approvals

Approval details

UL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 240868
---------------	---	---	---------------

EAC			B.01742
-----	---	--	---------
