

Mounting material - HC-ALU 6 MOUNT 150 GY - 2200912

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Mounting foot for panel mounting the HC-ALU panel mounting base

Your advantages

- Item is from the HC-ALU product range
- Aluminum press-drawn section
- Available in lengths from 100 mm ... 1000 mm, can be individually cut to any length
- Available in overall widths 53.5 mm ... 161 mm
- Degree of protection up to IP65
- Usable as handheld and wall housing
- Optional EMC seals available

Key Commercial Data

Packing unit	1 pc
Minimum order quantity	2 pc
GTIN	 4 046356 716864
GTIN	4046356716864
Weight per Piece (excluding packing)	50.000 g
Custom tariff number	76161000
Country of origin	Hungary

Technical data

General

Housing type	Panel mounting base
Color (RAL)	gray

Mounting material - HC-ALU 6 MOUNT 150 GY - 2200912

Technical data

Dimensions

Length	154.4 mm
--------	----------

Classifications

eCl@ss

eCl@ss 10.0.1	27182701
eCl@ss 4.0	27180400
eCl@ss 4.1	27180400
eCl@ss 5.0	27180500
eCl@ss 5.1	27180500
eCl@ss 6.0	27182000
eCl@ss 7.0	27182701
eCl@ss 8.0	27182701
eCl@ss 9.0	27182701

ETIM

ETIM 3.0	EC001031
ETIM 4.0	EC002498
ETIM 5.0	EC002779
ETIM 6.0	EC002779
ETIM 7.0	EC002779

UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501