

Side element - UM-ALU 4-100,5 COVER AL - 2200951

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Press-drawn section housings, Side elements (left and right), incl. snap-on foot, width: 105.4 mm, height: 2 mm



Your advantages

- ✓ Item is from the UM-ALU product range
- ✓ Aluminum press-drawn section
- ✓ Available in lengths from 42.5 mm ... 990 mm, can be cut to any length
- ✓ Available in overall widths of 75 mm and 105 mm
- ✓ Variety of connection technologies
- ✓ Can be mounted on the DIN rail
- ✓ EMC protection

Key Commercial Data

Packing unit	1 pc
GTIN	
GTIN	4046356716536
Weight per Piece (excluding packing)	40.000 g
Custom tariff number	76169910
Country of origin	Germany

Technical data

Product properties

Brief article description	Side element
Type	UM-ALU 4-100,5 COVER AL
Order No.	2200951

Side element - UM-ALU 4-100,5 COVER AL - 2200951

Technical data

Product properties

Housing type	Press-drawn section housings
Type	Side elements (left and right), incl. snap-on foot
Mounting type	Screw mounting

Dimensions

Width [w]	105.4 mm
Height [h]	2 mm
Depth [d]	31 mm

Material specifications

Material	Aluminum
Color	aluminum color
Surface characteristics	anodized

Ambient conditions

Ambient temperature (operation)	-40 °C ... 105 °C
---------------------------------	-------------------

Packaging specifications

Pieces per package	1
Denomination packing units	Pcs.

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 10.0.1	27182701
eCl@ss 4.0	27180400
eCl@ss 4.1	27180400
eCl@ss 5.0	27180500
eCl@ss 5.1	27180500
eCl@ss 6.0	27182000
eCl@ss 7.0	27182701
eCl@ss 8.0	27182701
eCl@ss 9.0	27182701

ETIM

ETIM 3.0	EC001031
----------	----------

Side element - UM-ALU 4-100,5 COVER AL - 2200951

Classifications

ETIM

ETIM 4.0	EC000721
ETIM 5.0	EC002779
ETIM 6.0	EC002779
ETIM 7.0	EC002779

UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501
UNSPSC 18.0	31261501
UNSPSC 19.0	31261501
UNSPSC 20.0	31261501
UNSPSC 21.0	31261501

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		B.01742
-----	---	---------

Accessories

Accessories

Component housing lower part

Side element - UM-ALU 4-100,5 COVER AL - 2200951

Accessories

Profile - UM-ALU 4-100,5 PROFILE 42,5 - 2200935



Press-drawn section housings, Basic profile, Profile width (internal): 100.5 mm, length: 42.5 mm

Profile - UM-ALU 4-100,5 PROFILE 60 - 2200936



Press-drawn section housings, Basic profile, Profile width (internal): 100.5 mm, length: 60 mm

Profile - UM-ALU 4-100,5 PROFILE 95 - 2200937



Press-drawn section housings, Basic profile, Profile width (internal): 100.5 mm, length: 95 mm

Profile - UM-ALU 4-100,5 PROFILE 130 - 2200938



Press-drawn section housings, Basic profile, Profile width (internal): 100.5 mm, length: 130 mm

Profile - UM-ALU 4-100,5 PROFILE 165 - 2200939



Press-drawn section housings, Basic profile, Profile width (internal): 100.5 mm, length: 165 mm

Side element - UM-ALU 4-100,5 COVER AL - 2200951

Accessories

Profile - UM-ALU 4-100,5 PROFILE 200 - 2200940



Press-drawn section housings, Basic profile, Profile width (internal): 100.5 mm, length: 200 mm

Profile - UM-ALU 4-100,5 PROFILE 235 - 2200941



Press-drawn section housings, Basic profile, Profile width (internal): 100.5 mm, length: 235 mm

Profile - UM-ALU 4-100,5 PROFILE 990 - 2200942



Press-drawn section housings, Basic profile, Profile width (internal): 100.5 mm, length: 990 mm
