

Housing cover - EH 22,5-C DS/ABS BK9005 - 2201254

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Component housing connection opening on both sides, Color: black, Width: 22.5 mm



Why buy this product

- Item is part of the EH product range
- Tool-free mounting
- Available in overall widths from 22.5 mm ... 90 mm
- Inflammability class HB acc. to UL 94
- Variety of connection technologies
- Can be mounted on the DIN rail or the wall

Key Commercial Data

Packing unit	1 STK
Minimum order quantity	10 STK
Weight per Piece (excluding packing)	14.000 g
Custom tariff number	85389099
Country of origin	India

Technical data

Standards and Regulations

Flammability rating according to UL 94	HB
--	----

Ambient conditions

Ambient temperature (operation)	-40 °C ... 80 °C (depending on power dissipation)
---------------------------------	---

Dimensions

Width	22.5 mm
-------	---------

Technical data

Flammability rating according to UL 94	HB
--	----

Standards and Regulations

Housing cover - EH 22,5-C DS/ABS BK9005 - 2201254

Technical data

Standards and Regulations

Flammability rating according to UL 94	HB
--	----

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values