

Housing cover - EH 45-C DS/ABS GY7035 - 2201512

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Component housing connection opening on both sides, Color: gray, Width: 45 mm



Why buy this product

- Item is part of the EH product range
- Tool-free mounting
- Available in overall widths from 22.5 mm ... 90 mm
- Flammability class HB acc. to UL 94
- Variety of connection technologies
- Can be mounted on the DIN rail or the wall

Key Commercial Data

| | |
|--------------------------------------|----------|
| Packing unit | 1 STK |
| Minimum order quantity | 10 STK |
| Weight per Piece (excluding packing) | 18.000 g |
| Custom tariff number | 85389099 |
| Country of origin | India |

Technical data

Standards and Regulations

| | |
|--|----|
| Flammability rating according to UL 94 | HB |
|--|----|

Ambient conditions

| | |
|---------------------------------|---|
| Ambient temperature (operation) | -40 °C ... 80 °C (depending on power dissipation) |
|---------------------------------|---|

Dimensions

| | |
|-------|-------|
| Width | 45 mm |
|-------|-------|

Technical data

| | |
|--|----|
| Flammability rating according to UL 94 | HB |
|--|----|

Standards and Regulations

Housing cover - EH 45-C DS/ABS GY7035 - 2201512

Technical data

Standards and Regulations

| | |
|--|----|
| Flammability rating according to UL 94 | HB |
|--|----|

Environmental Product Compliance

| | |
|------------|---|
| China RoHS | Environmentally friendly use period: unlimited = EFUP-e |
| | No hazardous substances above threshold values |