

## Upper part of housing - BC 161,6 OT 111112 BK - 2201977


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Upper part, Upper part, Color: black, Width: 161.6 mm, Length: 89.7 mm, Height: 62.2 mm

### Why buy this product

- Item is from the BC product range
- Conforms to DIN EN 43880
- Tool-free mounting
- Available in overall widths from one to nine width units (17.8 mm ... 161.6 mm)
- Inflammability class V0 according to UL 94
- Variety of connection technologies
- Can be mounted on the DIN rail or the wall
- Optional with bus connector for DIN rail mounting

### Key Commercial Data

Packing unit	1 STK
Minimum order quantity	500 STK
GTIN	 4 046356 950053
GTIN	4046356950053
Weight per Piece (excluding packing)	59.260 g
Custom tariff number	85472000
Country of origin	Germany

### Technical data

#### Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

### Classifications

eCl@ss

eCl@ss 5.1	27180506
------------	----------

## Upper part of housing - BC 161,6 OT 111112 BK - 2201977

### Classifications

#### eCl@ss

eCl@ss 6.0	27180802
eCl@ss 8.0	27182702
eCl@ss 9.0	27182702

#### ETIM

ETIM 4.0	EC000437
ETIM 5.0	EC001031
ETIM 6.0	EC001031

#### UNSPSC

UNSPSC 13.2	31261501
-------------	----------