

Side element - UM-BASIC/PRO 72 COVER-R KMGY - 2202019

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Lateral element (right) with mounting foot for DIN rails for UM-BASIC profiles with a PCB width of 72 mm



Your advantages

- ✓ Different base profiles, each with three PCB levels
- ✓ Module covers of different geometries can be positioned in any way
- ✓ Compatibility with many standard connection technologies
- ✓ Easy device mounting thanks to snap-mount principle (the sides are fixed without the aid of tools)
- ✓ High degree of flexibility, thanks to freely positionable covering hoods



Key Commercial Data

Packing unit	1 pc
Minimum order quantity	10 pc
GTIN	 4 055626 005317
GTIN	4055626005317
Weight per Piece (excluding packing)	14.000 g
Custom tariff number	39269097
Country of origin	Poland

Technical data

Product properties

Brief article description	Side element
Type	UM-BASIC/PRO 72 COVER-R KMGY
Order No.	2202019
Housing type	Press-drawn section housings

Side element - UM-BASIC/PRO 72 COVER-R KMGY - 2202019

Technical data

Product properties

Type	Lateral element (right)
Mounting type	DIN rail mounting/wall mounting (with optional mounting flange)

Dimensions

Profile PCB width (selectable):	72 mm [UM72]
Width [w]	19.5 mm
Height [h]	92.3 mm
Depth [d]	39.45 mm
Depth from top edge of DIN rail [d]	32.45 mm

Material specifications

Housing material	Polyamide
Color (RAL)	light gray (7035)
Flammability rating according to UL 94	V0

Ambient conditions

Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Relative humidity (storage/transport)	80 %

PCB specifications

PCB holders	3
PCB thickness	1.4 mm ... 1.8 mm
PCB surface	700 mm ² ... 1200 mm ² (per basic profile cm)
Type of PCB mount	Insertion/securing with additional elements

Mechanical strength/tumbling barrel

Specification	IEC 60998-1:2002-12
Height of fall	50 cm
Number of drop cycles	10

Thermal stability (ball thrust test)

Specification	IEC 60695-10-2:2014-02
Temperature	125 °C
Test duration	1 h
Force	20 N

Test for assessing the risk of fire (glow wire)

Specification	DIN EN 60695-2-11 (VDE 0471-2-11):2014-11
Temperature	850 °C

Side element - UM-BASIC/PRO 72 COVER-R KMGY - 2202019

Technical data

Test for assessing the risk of fire (glow wire)

Time of exposure	30 s
------------------	------

General information

Type of note	Assembly instruction:
Note	Refer to the data sheet for the range in the download area.

Packaging specifications

Type of packaging	packed in cardboard
Pieces per package	10
Denomination packing units	Pcs.
Outer packaging type	Carton

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 10.0.1	27182701
eCl@ss 5.0	27180500
eCl@ss 5.1	27180500
eCl@ss 6.0	27400500
eCl@ss 7.0	27182701
eCl@ss 8.0	27182701
eCl@ss 9.0	27182701

ETIM

ETIM 5.0	EC002779
ETIM 6.0	EC002779
ETIM 7.0	EC002779

UNSPSC

UNSPSC 13.2	31261501
UNSPSC 18.0	31261501
UNSPSC 19.0	31261501
UNSPSC 20.0	31261501
UNSPSC 21.0	31261501

Side element - UM-BASIC/PRO 72 COVER-R KMGY - 2202019

Approvals


Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		B.01742
-----	---	---------

Accessories

Accessories

Screwdriver tools

Screwdriver - SZF 0-0,4X2,5 - 1204504



Actuation tool, for ST terminal blocks, also suitable for use as a bladed screwdriver, size: 0.4 x 2.5 x 75 mm, 2-component grip, with non-slip grip

Necessary add-on products

Profile - UM-BASIC PROFILE - 2200149



Press-drawn section housings, Basic profile, profile length (configurable): 3 cm ... 100 cm, color: light gray (7035), Note: required profile length = PCB length - 16.2 mm

Side element - UM-BASIC/PRO 72 COVER-R KMGY - 2202019

Accessories

Side element - UM-BASIC/PRO 72 COVER-L KMGY - 2202018



Lateral element (left) with mounting foot for DIN rails for UM-BASIC profiles with a PCB width of 72 mm

Additional products

Functional earth ground contact - UM-BASIC/PRO PE CONTACT L1 - 2202025



PE contact for UM-BASIC panel mounting base for connecting the PCB to the DIN rail at level 1

Functional earth ground contact - UM-BASIC/PRO PE CONTACT L2 - 2202026



PE contact for UM-BASIC panel mounting base for connecting the PCB to the DIN rail at level 2

Functional earth ground contact - UM-BASIC/PRO PE CONTACT L3 - 2202027



PE contact for UM-BASIC panel mounting base for connecting the PCB to the DIN rail at level 3

Mounting material - UM-BASIC/PRO PCB S-LOCK KMGY - 2202031



Locking element for locking the upper PCB onto UM-BASIC/PRO housings close to the edge

Side element - UM-BASIC/PRO 72 COVER-R KMGY - 2202019

Accessories

Mounting material - UM-BASIC/PRO PCB C-LOCK L1KMGY - 2202028



Locking element for locking the PCB onto UM-BASIC/PRO housing at level 1

Mounting material - UM-BASIC/PRO PCB C-LOCK L2KMGY - 2202029



Locking element for locking the PCB onto UM-BASIC/PRO housing at level 2

Mounting material - UM-BASIC/PRO PCB C-LOCK L3KMGY - 2202030



Locking element for locking the PCB onto UM-BASIC/PRO housing at level 3

Mounting flange - UM-BASIC/PRO MOUNT KMGY - 2202032

Press-drawn section housings, Mounting flange for direct wall mounting, color: light gray (7035)



Foot element - UM-BASIC/PRO 72 FOOT KMGY - 2202020

Press-drawn section housings, for the DIN rail, for mounting below UM-BASIC PROFILE (width: 72 mm), Foot element, color: light gray (7035)



Side element - UM-BASIC/PRO 72 COVER-R KMGY - 2202019

Accessories

Covering hood - UM-BASIC/PRO A/U N 73 CM - 2202035



Press-drawn section housings, Cover, width: 73 mm, profile length (configurable): 3 cm ... 100 cm, height: 24 mm, color: transparent, Note: max. length of the cover = PCB length = 19 mm

Covering hood - UM-BASIC/PRO A/U 73 CM - 2202036



Press-drawn section housings, Cover, width: 73 mm, profile length (configurable): 3 cm ... 100 cm, height: 63.2 mm, color: transparent, Note: max. length of the cover = PCB length = 19 mm

Covering hood - UM-BASIC/PRO A/U 92 CM - 2202037



Press-drawn section housings, Cover, width: 92 mm, profile length (configurable): 3 cm ... 100 cm, height: 34 mm, color: transparent, Note: max. length of the cover = PCB length = 19 mm

Side element - UM-BASIC/PRO LID-73N KMGY - 2202034



Press-drawn section housings, Side element for low U-shaped profile cover, width: 10.35 mm, height: 78.43 mm, color: light gray (7035)

Side element - UM-BASIC/PRO LID-73 KMGY - 2202033



Press-drawn section housings, Side element for U-shaped profile cover, width: 10.35 mm, height: 78.49 mm, color: light gray (7035)

Side element - UM-BASIC/PRO 72 COVER-R KMGY - 2202019

Accessories

Side element - UM-BASIC/PRO LID-92 KMGY - 2202047



Press-drawn section housings, Side element for U-shaped profile cover, width: 10.35 mm, height: 97.51 mm, color: light gray (7035)