

Printed-circuit board connector - HSCH 1,5-3U/18 9005 - 2202232

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




HSC header, touch-proof, 3 units, 18 connections, please note the positioning, color: black

Why buy this product

- ✓ Item is from the ME-IO product range
- ✓ Tool-free mounting
- ✓ Available in overall widths from 18.8 mm
- ✓ Inflammability class V0 according to UL 94
- ✓ Front push-in connection technology
- ✓ Can be mounted on the DIN rail
- ✓ Optional with bus connector for DIN rail mounting



Key Commercial Data

Packing unit	1 STK
Minimum order quantity	50 STK
GTIN	 4 055626 023700
GTIN	4055626023700
Weight per Piece (excluding packing)	5.600 g
Custom tariff number	85366930
Country of origin	Germany

Technical data

Dimensions

Length	16 mm
Pitch	3.45 mm

Printed-circuit board connector - HSCH 1,5-3U/18 9005 - 2202232

Technical data

Dimensions

Width	12.45 mm
-------	----------

General

Connection in acc. with standard	EN-VDE
Nominal current I _N	8 A
Flammability rating according to UL 94	V0
Color	black
Number of positions	18

Standards and Regulations

Connection in acc. with standard	EN-VDE
Flammability rating according to UL 94	V0

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Approvals


Approvals

Approvals

cULus Recognized

Ex Approvals

Approval details

cULus Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	E60425-20150613
		B	
Nominal current I _N		8 A	
Nominal voltage U _N		150 V	