

## Cable - CABLE-D37SUB/B/B/ 300/KONFEK/S - 2305525

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Assembled, shielded circular cable, with D-SUB socket strip, 37-pos. from both sides, cable length: 3 m



### Key Commercial Data

Packing unit	1 pc
Weight per Piece (excluding packing)	714.2 g
Custom tariff number	85444290
Country of origin	Germany

### Technical data

#### General

Nominal voltage $U_N$	125 V AC/DC
Max. current carrying capacity per path	2 A
Max. conductor resistance	$\leq 0.09 \Omega/m$
Length of cable	3 m
Single wire, cross section	0.25 mm <sup>2</sup>
Single wire, cross section [AWG]	24
External diameter	12 mm
Shielding	yes
	Tinned copper-braided shield, approx. 85% covering
Insertion/withdrawal cycles	> 200

#### Environmental conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C
Flame resistance	IEC 60332-1
	DIN VDE 0482 Part 332-1

#### Connector, module side

Connection name	Field level
-----------------	-------------

## Cable - CABLE-D37SUB/B/B/ 300/KONFEK/S - 2305525

### Technical data

#### Connector, module side

Connection method	D-SUB socket strip
Number of connections	1
Number of positions	37

#### Connector, controller side

Connection name	Controller level
Connection method	D-SUB socket strip
Number of connections	1
Number of positions	37

### Standards and Regulations

Connection in acc. with standard	CUL
Flame resistance	IEC 60332-1
	DIN VDE 0482 Part 332-1

### Classifications

#### eCl@ss

eCl@ss 4.0	27060306
eCl@ss 4.1	27060306
eCl@ss 5.0	27061801
eCl@ss 5.1	27061801
eCl@ss 6.0	27061801
eCl@ss 7.0	27061801
eCl@ss 8.0	27249205
eCl@ss 9.0	27242220

#### ETIM

ETIM 2.0	EC000237
ETIM 3.0	EC000237
ETIM 4.0	EC000237
ETIM 5.0	EC000237

#### UNSPSC

UNSPSC 6.01	26121620
UNSPSC 7.0901	26121620
UNSPSC 11	26121620
UNSPSC 12.01	26121620
UNSPSC 13.2	26121620

# Cable - CABLE-D37SUB/B/B/ 300/KONFEK/S - 2305525

## Approvals

### Approvals

---

#### Approvals

UL Recognized / cUL Recognized / CSA / EAC / cULus Recognized

---

#### Ex Approvals


---

#### Approvals submitted

---

### Approval details

UL Recognized 

cUL Recognized 

CSA 

EAC

cULus Recognized 