

Cable gland - PSD-S AS CABLE GLAND M16X1,5 - 2700145


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



M16 cable threaded joint x 1.5 mm, black



Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 491372
GTIN	4046356491372
Weight per Piece (excluding packing)	12.600 g
Custom tariff number	39269097
Country of origin	Germany

Technical data

Dimensions

Diameter	18 mm
Height	35 mm

Ambient conditions

Ambient temperature (operation)	-30 °C ... 60 °C
---------------------------------	------------------

General

Material	PA
Color	black
Weight	10 g
Mounting position	any
Scope of delivery	1 x nut

Cable gland - PSD-S AS CABLE GLAND M16X1,5 - 2700145

Technical data

General

Wrench size	19.00 mm
Cable diameter	5 mm ... 10 mm

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 4.0	27250313
eCl@ss 4.1	27250313
eCl@ss 5.0	27149109
eCl@ss 5.1	27149100
eCl@ss 6.0	27149100
eCl@ss 7.0	27149109
eCl@ss 8.0	27149109
eCl@ss 9.0	27371232

ETIM

ETIM 3.0	EC000441
ETIM 4.0	EC000441
ETIM 5.0	EC000441
ETIM 6.0	EC000441
ETIM 7.0	EC000441

UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	39121311
UNSPSC 12.01	39121311
UNSPSC 13.2	39121311

Approvals

Approvals

Cable gland - PSD-S AS CABLE GLAND M16X1,5 - 2700145

Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC



RU *-
DE.A*30.B.00237