

## Mounting material - PSD-S ME OB - 2700153

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Outlet box with lateral cable entry for floor and base mounting

### Your advantages

- One-sided assembly for up to 5 signal elements

### Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 491440
GTIN	4046356491440
Weight per Piece (excluding packing)	80.000 g
Custom tariff number	39269097
Country of origin	Germany

### Technical data

#### Dimensions

Diameter	70 mm
Height	28.5 mm

#### Ambient conditions

Ambient temperature (operation)	-30 °C ... 60 °C
---------------------------------	------------------

#### General

Material	PA-GF
Color	black
Weight	73 g

## Mounting material - PSD-S ME OB - 2700153

### Technical data

#### General

Mounting position	any
Mounting type	Base mounting Tube mounting
Scope of delivery	4 x plastic screw 1 x cable threaded joint 1 x nut

#### Connection data

Connection method	Screw connection
-------------------	------------------

#### Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

### Classifications

#### eCl@ss

eCl@ss 4.0	27143203
eCl@ss 4.1	27143203
eCl@ss 5.0	27371232
eCl@ss 5.1	27371200
eCl@ss 6.0	27371200
eCl@ss 7.0	27371232
eCl@ss 8.0	27371232
eCl@ss 9.0	27371232

#### ETIM

ETIM 3.0	EC001152
ETIM 4.0	EC001152
ETIM 5.0	EC001152
ETIM 6.0	EC001152
ETIM 7.0	EC001152

#### UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	39121311
UNSPSC 12.01	39121311
UNSPSC 13.2	39121311

## Mounting material - PSD-S ME OB - 2700153

### Approvals

Approvals

---

Approvals


EAC / EAC

---

Ex Approvals

---

### Approval details

EAC		EAC-Zulassung
-----	---	---------------

EAC		RU *- DE.A*30.B.00237
-----	--	--------------------------

---