

## Inline terminal - FMC-IB IL 24 DO8/HD-PAC - 2700890

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Inline, Digital output terminal, Digital outputs: 8, 24 V DC, 500 mA, Connection technology: 1-wire, Transmission speed in the local bus 500 kbps, Degree of protection IP20, including Inline connector and labeling field



### Key Commercial Data

Packing unit	1 STK
Minimum order quantity	100 STK
GTIN	 4 046356 657914
GTIN	4046356657914
Weight per Piece (excluding packing)	80.000 g
Custom tariff number	85389091
Country of origin	Germany

### Technical data

#### Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

### Classifications

#### eCl@ss

eCl@ss 4.0	27240404
eCl@ss 4.1	27240404
eCl@ss 5.0	27242204
eCl@ss 5.1	27242604
eCl@ss 6.0	27242604
eCl@ss 7.0	27242604
eCl@ss 8.0	27242604
eCl@ss 9.0	27242604

## Inline terminal - FMC-IB IL 24 DO8/HD-PAC - 2700890

### Classifications

#### ETIM

ETIM 2.0	EC001433
ETIM 3.0	EC001599
ETIM 4.0	EC001599
ETIM 5.0	EC001599
ETIM 6.0	EC001599

#### UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	39121311
UNSPSC 12.01	39121311
UNSPSC 13.2	32151602