

TT-UK5/220DC

This item is no longer available. Should you have any questions, please contact our Sales Team.

Order No.: 2794738

The illustration shows version TT-UK5- 24 DC



<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=2794738>

Modular terminal block with surge voltage fine protection between clamping connector and DIN rail, nominal voltage: 220 V DC, for mounting on NS 32 or NS 35/7.5, terminal width: 6.2 mm, terminal height: 47 mm

Commercial data

EAN	4017918118846
Pack	50 pcs.
Customs tariff	85363030
Weight/Piece	0.01111 KG

Product notes

WEEE/RoHS-compliant since:
06/28/2006



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

General

Housing material	PA
Inflammability class acc. to UL 94	V2
Ambient temperature (operation)	-40 °C ... 85 °C

Protective circuit

Nominal voltage U_N	220 V DC
Nominal current I_N	32 A (50°C)
Discharge current to PE at U_C	$\leq 5 \mu\text{A}$
Nominal discharge surge current I_n (8/20) μs (Core-Earth)	47 A
Nominal pulse current I_{an} (10/1000) μs (Core-Earth)	5 A

Connection data

Type of connection	Screw terminal blocks
Screw thread	M3
Tightening torque, min	0.5 Nm
Stripping length	8 mm
Conductor cross section stranded min.	0.2 mm ²
Conductor cross section stranded max.	4 mm ²
Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	4 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	12

Accessories

Item	Designation	Description
Assembly		
2794990	D-TERMITRAB-UK 5	Cover for setting the end of a TT-UK 5 row of terminal blocks, color: black

Address

PHOENIX CONTACT Inc., USA
586 Fulling Mill Road
Middletown, PA 17057, USA
Phone (800) 888-7388
Fax (717) 944-1625
<http://www.phoenixcon.com>



© 2009 Phoenix Contact
Technical modifications reserved;