

## Component connector - ST-BE-VP - 2802332

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Component plug, for 4-pos. components, two basic terminal blocks required per plug, 19 mm high

The figure shows ST-BE

### Key Commercial Data

Packing unit	1 pc
Minimum order quantity	10 pc
GTIN	 4 017918 074425
Weight per Piece (excluding packing)	13.93 g
Custom tariff number	85366990
Country of origin	Poland

### Technical data

#### Technical data

Color	gray
Pitch	12 mm
Flammability rating according to UL 94	V0

#### Standards and Regulations

Connection in acc. with standard	CUL
Flammability rating according to UL 94	V0

### Classifications

#### eCl@ss

eCl@ss 4.0	27141199
eCl@ss 4.1	27141199
eCl@ss 5.0	27141145

# Component connector - ST-BE-VP - 2802332

## Classifications

### eCl@ss

eCl@ss 5.1	27141145
eCl@ss 6.0	27141149
eCl@ss 7.0	27141149
eCl@ss 8.0	27141149

### ETIM

ETIM 2.0	EC000897
ETIM 3.0	EC000897
ETIM 4.0	EC002018
ETIM 5.0	EC002018

### UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121409
UNSPSC 11	39121409
UNSPSC 12.01	39121409
UNSPSC 13.2	39121409

## Approvals

### Approvals

---

#### Approvals

UL Recognized / cUL Recognized / EAC / cULus Recognized

---

#### Ex Approvals

---

#### Approvals submitted

---


### Approval details

UL Recognized	
mm <sup>2</sup> /AWG/kcmil	30-14


## Component connector - ST-BE-VP - 2802332

### Approvals

Nominal current I <sub>N</sub>	10 A
Nominal voltage U <sub>N</sub>	300 V

cUL Recognized 	
mm <sup>2</sup> /AWG/kcmil	30-14
Nominal current I <sub>N</sub>	10 A
Nominal voltage U <sub>N</sub>	300 V

EAC
-----

cULus Recognized 
---