

# FL CAT6 PATCH 20,0 - Patch cable

2891576

<https://www.phoenixcontact.com/de/produkte/2891576>



Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.

Patch cable, CAT6, pre-assembled, 20.0 m



## Commercial Data

Item number	2891576
Packing unit	1 pc
Minimum order quantity	1 pc
Sales Key	O1 - Automatisierungssys.
Product Key	ABNABG
Catalog Page	Page 721 (C-2-2019)
GTIN	4046356185028
Weight per Piece (including packing)	779,3 g
Weight per Piece (excluding packing)	714,1 g
Customs tariff number	85444210
Country of origin	PL

# FL CAT6 PATCH 20,0 - Patch cable



2891576

<https://www.phoenixcontact.com/de/produkte/2891576>

## Technical Data

### Product properties

Product type	Data cable preassembled
Number of positions	8
Sensor type	Ethernet
Connection profile	RJ45

### Electrical properties

Contact resistance	$\leq 0.003 \Omega$ (IEC 60603-7)
Nominal voltage $U_N$	150 V <sub>rms</sub>
Nominal current $I_N$	1.5 A
Transmission speed	1 Gbps

### Material specifications

Flammability rating according to UL 94	V0
Outer sheath, material	LSFROH

### Dimensions

#### External dimensions

External diameter max.	6.2 mm
------------------------	--------

### Connector

#### Connection 1

Type	Plug straight RJ45
------	--------------------

#### Connection 2

Type	Plug straight RJ45
------	--------------------

### Cable/line

Cable length	20.00 m
External cable diameter	5.50 mm
Outer sheath, material	LSFROH
Single wire, number of litz wires	8
Single wire, material	Cu litz wire
Single wire, cross section	0.14 mm <sup>2</sup>
Shielding	S/FTP
Smallest bending radius, fixed installation	30 mm
Halogen-free	according to IEC 60754-1
Concentration of fumes	in accordance with IEC 61034
Flame resistance	according to IEC 60332-3C

### Environmental and real-life conditions

# FL CAT6 PATCH 20,0 - Patch cable



2891576

<https://www.phoenixcontact.com/de/produkte/2891576>

## Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-10 °C ... 60 °C

## Standards and regulations

Flame resistance	according to IEC 60332-3C
Concentration of fumes	in accordance with IEC 61034

# FL CAT6 PATCH 20,0 - Patch cable

2891576

<https://www.phoenixcontact.com/de/produkte/2891576>



## Approvals



**EAC**

Approval ID: 19060508

# FL CAT6 PATCH 20,0 - Patch cable



2891576

<https://www.phoenixcontact.com/de/produkte/2891576>

## Classifications

### ECLASS

ECLASS-11.0	27060308
ECLASS-12.0	27060308
ECLASS-13.0	27060308

### ETIM

ETIM 8.0	EC002599
----------	----------

### UNSPSC

UNSPSC 21.0	26121600
-------------	----------

# FL CAT6 PATCH 20,0 - Patch cable

2891576

<https://www.phoenixcontact.com/de/produkte/2891576>



## Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

# FL CAT6 PATCH 20,0 - Patch cable

2891576

<https://www.phoenixcontact.com/de/produkte/2891576>



## Accessories

### NBC-R40C/0,3-BC5/R40C - Patch cable

1227558

<https://www.phoenixcontact.com/de/produkte/1227558>



Patch cable, degree of protection: IP20, cable length: 0.3 m, number of positions: 8, CAT5, connection method: Pierce connection, connection cross section: AWG 26- 26, cable outlet: straight, Ethernet

---

### NBC-R40C/0,5-BC5/R40C - Patch cable

1227559

<https://www.phoenixcontact.com/de/produkte/1227559>



Patch cable, degree of protection: IP20, cable length: 0.5 m, number of positions: 8, CAT5, connection method: Pierce connection, connection cross section: AWG 26- 26, cable outlet: straight, Ethernet

# FL CAT6 PATCH 20,0 - Patch cable

2891576

<https://www.phoenixcontact.com/de/produkte/2891576>



## NBC-R4OC/1,0-BC5/R4OC - Patch cable

1227560

<https://www.phoenixcontact.com/de/produkte/1227560>



Patch cable, degree of protection: IP20, cable length: 1 m, number of positions: 8, CAT5, connection method: Pierce connection, connection cross section: AWG 26- 26, cable outlet: straight, Ethernet

---

## NBC-R4OC/1,5-BC5/R4OC - Patch cable

1227561

<https://www.phoenixcontact.com/de/produkte/1227561>



Patch cable, degree of protection: IP20, cable length: 1.5 m, number of positions: 8, CAT5, connection method: Pierce connection, connection cross section: AWG 26- 26, cable outlet: straight, Ethernet

# FL CAT6 PATCH 20,0 - Patch cable

2891576

<https://www.phoenixcontact.com/de/produkte/2891576>



## NBC-R4OC/2,0-BC5/R4OC - Patch cable

1227562

<https://www.phoenixcontact.com/de/produkte/1227562>



Patch cable, degree of protection: IP20, cable length: 2 m, number of positions: 8, CAT5, connection method: Pierce connection, connection cross section: AWG 26- 26, cable outlet: straight, Ethernet

---

## NBC-R4OC/3,0-BC5/R4OC - Patch cable

1227563

<https://www.phoenixcontact.com/de/produkte/1227563>



Patch cable, degree of protection: IP20, cable length: 3 m, number of positions: 8, CAT5, connection method: Pierce connection, connection cross section: AWG 26- 26, cable outlet: straight, Ethernet

# FL CAT6 PATCH 20,0 - Patch cable

2891576

<https://www.phoenixcontact.com/de/produkte/2891576>



## NBC-R4OC/5,0-BC5/R4OC - Patch cable

1227564

<https://www.phoenixcontact.com/de/produkte/1227564>



Patch cable, degree of protection: IP20, cable length: 5 m, number of positions: 8, CAT5, connection method: Pierce connection, connection cross section: AWG 26- 26, cable outlet: straight, Ethernet

---

## NBC-R4OC/7,5-BC5/R4OC - Patch cable

1227565

<https://www.phoenixcontact.com/de/produkte/1227565>



Patch cable, degree of protection: IP20, cable length: 7.5 m, number of positions: 8, CAT5, connection method: Pierce connection, connection cross section: AWG 26- 26, cable outlet: straight, Ethernet

# FL CAT6 PATCH 20,0 - Patch cable

2891576

<https://www.phoenixcontact.com/de/produkte/2891576>



## NBC-R4OC/0,3-BC6A/R4OC - Patch cable

1227572

<https://www.phoenixcontact.com/de/produkte/1227572>



Patch cable, degree of protection: IP20, cable length: 0.3 m, number of positions: 8, 10 Gbps, CAT6<sub>A</sub>, connection method: Pierce connection, connection cross section: AWG 26- 26, cable outlet: straight, Ethernet

---

## NBC-R4OC/0,5-BC6A/R4OC - Patch cable

1227573

<https://www.phoenixcontact.com/de/produkte/1227573>



Patch cable, degree of protection: IP20, cable length: 0.5 m, number of positions: 8, 10 Gbps, CAT6<sub>A</sub>, connection method: Pierce connection, connection cross section: AWG 26- 26, cable outlet: straight, Ethernet

## FL CAT6 PATCH 20,0 - Patch cable

2891576

<https://www.phoenixcontact.com/de/produkte/2891576>



### NBC-R4OC/1,0-BC6A/R4OC - Patch cable

1227575

<https://www.phoenixcontact.com/de/produkte/1227575>



Patch cable, degree of protection: IP20, cable length: 1 m, number of positions: 8, 10 Gbps, CAT6<sub>A</sub>, connection method: Pierce connection, connection cross section: AWG 26- 26, cable outlet: straight, Ethernet

---

### NBC-R4OC/1,5-BC6A/R4OC - Patch cable

1227578

<https://www.phoenixcontact.com/de/produkte/1227578>



Patch cable, degree of protection: IP20, cable length: 1.5 m, number of positions: 8, 10 Gbps, CAT6<sub>A</sub>, connection method: Pierce connection, connection cross section: AWG 26- 26, cable outlet: straight, Ethernet

# FL CAT6 PATCH 20,0 - Patch cable

2891576

<https://www.phoenixcontact.com/de/produkte/2891576>



## NBC-R4OC/2,0-BC6A/R4OC - Patch cable

1227580

<https://www.phoenixcontact.com/de/produkte/1227580>



Patch cable, degree of protection: IP20, cable length: 2 m, number of positions: 8, 10 Gbps, CAT6<sub>A</sub>, connection method: Pierce connection, connection cross section: AWG 26- 26, cable outlet: straight, Ethernet

---

## NBC-R4OC/3,0-BC6A/R4OC - Patch cable

1227581

<https://www.phoenixcontact.com/de/produkte/1227581>



Patch cable, degree of protection: IP20, cable length: 3 m, number of positions: 8, 10 Gbps, CAT6<sub>A</sub>, connection method: Pierce connection, connection cross section: AWG 26- 26, cable outlet: straight, Ethernet

## FL CAT6 PATCH 20,0 - Patch cable

2891576

<https://www.phoenixcontact.com/de/produkte/2891576>



## NBC-R4OC/5,0-BC6A/R4OC - Patch cable

1227583

<https://www.phoenixcontact.com/de/produkte/1227583>



Patch cable, degree of protection: IP20, cable length: 5 m, number of positions: 8, 10 Gbps, CAT6<sub>A</sub>, connection method: Pierce connection, connection cross section: AWG 26- 26, cable outlet: straight, Ethernet

---

## NBC-R4OC/7,5-BC6A/R4OC - Patch cable

1227585

<https://www.phoenixcontact.com/de/produkte/1227585>



Patch cable, degree of protection: IP20, cable length: 7.5 m, number of positions: 8, 10 Gbps, CAT6<sub>A</sub>, connection method: Pierce connection, connection cross section: AWG 26- 26, cable outlet: straight, Ethernet

## FL CAT6 PATCH 20,0 - Patch cable

2891576

<https://www.phoenixcontact.com/de/produkte/2891576>



## NBC-R4OC/10,0-BC6A/R4OC - Patch cable

1227588

<https://www.phoenixcontact.com/de/produkte/1227588>



Patch cable, degree of protection: IP20, cable length: 10 m, number of positions: 8, 10 Gbps, CAT6<sub>A</sub>, connection method: Pierce connection, connection cross section: AWG 26- 26, cable outlet: straight, Ethernet

---

## NBC-R4OC/12,5-BC6A/R4OC - Patch cable

1227590

<https://www.phoenixcontact.com/de/produkte/1227590>



Patch cable, degree of protection: IP20, cable length: 12.5 m, number of positions: 8, 10 Gbps, CAT6<sub>A</sub>, connection method: Pierce connection, connection cross section: AWG 26- 26, cable outlet: straight, Ethernet

# FL CAT6 PATCH 20,0 - Patch cable

2891576

<https://www.phoenixcontact.com/de/produkte/2891576>



## NBC-R4OC/15,0-BC6A/R4OC - Patch cable

1227591

<https://www.phoenixcontact.com/de/produkte/1227591>



Patch cable, degree of protection: IP20, cable length: 15 m, number of positions: 8, 10 Gbps, CAT6<sub>A</sub>, connection method: Pierce connection, connection cross section: AWG 26- 26, cable outlet: straight, Ethernet

---

## NBC-R4OC/20,0-BC6A/R4OC - Patch cable

1227593

<https://www.phoenixcontact.com/de/produkte/1227593>



Patch cable, degree of protection: IP20, cable length: 20 m, number of positions: 8, 10 Gbps, CAT6<sub>A</sub>, connection method: Pierce connection, connection cross section: AWG 26- 26, cable outlet: straight, Ethernet

---

Phoenix Contact 2023 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT Deutschland GmbH  
Flachsmarktstraße 8  
D-32825 Blomberg  
+49 52 35/3-1 20 00  
[info@phoenixcontact.de](mailto:info@phoenixcontact.de)