

## Upper part of housing - BC 71,6 OT U22 KMGY - 2896063

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Installation component housing, Upper part, Color: light gray, Width: 71.6 mm, Constructional height: 62.2 mm

### Product Features

- Item is from the BC product range
- Conforms to DIN EN 43880
- Tool-free mounting
- Available in overall widths from one to nine width units (17.8 mm ... 161.6 mm)
- Inflammability class V0 according to UL 94
- Variety of connection technologies
- Can be mounted on the DIN rail or the wall
- Optional with bus connector for DIN rail mounting

### Key Commercial Data

Packing unit	1 pc
Minimum order quantity	10 pc
Weight per Piece (excluding packing)	29.8 g
Custom tariff number	85472000
Country of origin	Germany

### Technical data

#### General

Housing type	Installation component housing
Housing material	Polycarbonate
Color	light gray

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
---------------------------------	----------------------------------------------------

#### Dimensions

Length	89.7 mm
--------	---------

## Upper part of housing - BC 71,6 OT U22 KMGY - 2896063

### Technical data

#### Dimensions

Constructional height	62.2 mm
Width	71.6 mm

#### Technical data

Flammability rating according to UL 94	V0
----------------------------------------	----

#### Standards and Regulations

Flammability rating according to UL 94	V0
----------------------------------------	----

### Classifications

#### eCl@ss

eCl@ss 4.0	27180401
eCl@ss 4.1	27180401
eCl@ss 5.0	27180506
eCl@ss 5.1	27180506
eCl@ss 6.0	27180802
eCl@ss 7.0	27182702
eCl@ss 8.0	27182702

#### ETIM

ETIM 2.0	EC001031
ETIM 3.0	EC001031
ETIM 4.0	EC000886
ETIM 5.0	EC001031

#### UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501

### Approvals

#### Approvals

---

Approvals

UL Recognized / EAC

## Upper part of housing - BC 71,6 OT U22 KMGY - 2896063

### Approvals

---

Ex Approvals

---

Approvals submitted

---

### Approval details

