

Filler plugs - BC 35,6 BS U11 KMGY - 2896209

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Installation component housing, Filler plug; 35.6, width: 35.6 mm, color: Light gray (7035)

Your advantages

- Item is from the BC product range
- Conforms to DIN EN 43880
- Tool-free mounting
- Available in overall widths from one to nine width units (17.8 mm ... 161.6 mm)
- Inflammability class V0 according to UL 94
- Variety of connection technologies
- Can be mounted on the DIN rail or the wall
- Optional with bus connector for DIN rail mounting

Key Commercial Data

Packing unit	1 pc
GTIN	
GTIN	4046356096607
Weight per Piece (excluding packing)	3.490 g
Custom tariff number	85472000
Country of origin	Germany

Technical data

Item properties

Brief article description	Filler plugs
Type	BC 35,6 BS U11 KMGY

Filler plugs - BC 35,6 BS U11 KMGY - 2896209

Technical data

Item properties

Order No.	2896209
Housing type	Installation component housing
Type	Filler plug; 35.6

Dimensions

Width [w]	35.6 mm
Depth [d]	11.05 mm

Material data

Color (RAL)	Light gray (7035)
Housing material	Polyamide

Packaging information

Pieces per package	50
Denomination packing units	Pcs.

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 4.0	27180401
eCl@ss 4.1	27180401
eCl@ss 5.0	27180506
eCl@ss 5.1	27180500
eCl@ss 6.0	27180800
eCl@ss 7.0	27182702
eCl@ss 8.0	27182702
eCl@ss 9.0	27182702

ETIM

ETIM 2.0	EC001031
ETIM 3.0	EC001031
ETIM 4.0	EC001031
ETIM 5.0	EC001031
ETIM 6.0	EC001031
ETIM 7.0	EC001031

Filler plugs - BC 35,6 BS U11 KMGY - 2896209

Classifications

UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501

Approvals


Approvals

Approvals

UL Recognized / EAC

Ex Approvals

Approval details

UL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 240868
---------------	---	---	---------------

EAC			B.01742
-----	---	--	---------