

## Cable - CAB-DSUB37F/RA/OE/22/S/ 3M - 2906396

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Assembled shielded round cable; connection 1: Single wires (37-position) (The wires are marked and fitted with ferrules.); connection 2: (); cable length: 3 m

### Your advantages

- Individual wire marking: 1, 2, 3, 4, etc.
- Individual wires fitted with ferrules
- Screw connection: 2 UNC 4-40 screws
- Open end at one end
- D-SUB socket or pin strip at one end
- 1:1 connection

### Key Commercial Data

Packing unit	1 pc
GTIN	 4 055626 337418
GTIN	4055626337418
Weight per Piece (excluding packing)	750.000 g
Custom tariff number	85444290
Country of origin	United States

### Technical data

#### Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

#### General

Max. permissible operating voltage	125 V AC
------------------------------------	----------

## Cable - CAB-DSUB37F/RA/OE/22/S/ 3M - 2906396

### Technical data

#### General

	125 V DC
Max. current carrying capacity per path	2 A
Length of cable	3 m
External cable diameter	11.7 mm
Single wire, cross section	0.36 mm <sup>2</sup>
Single wire, cross section [AWG]	22
Shielding	yes
	Overall foil and braid shield

#### Connection data

Connection name	Field level
Connection method	D-SUB socket strip
Number of connections	1
Number of positions	37

#### Connection data 2

Connection name	Controller level
Connection method	Single wires
Number of positions	37
Note	The wires are marked and fitted with ferrules.

#### Supported controller

Controller	universal
------------	-----------

### Classifications

#### eCl@ss

eCl@ss 5.0	27242200
eCl@ss 5.1	27242200
eCl@ss 6.0	27249200
eCl@ss 7.0	27249205
eCl@ss 8.0	27249205
eCl@ss 9.0	27242220

#### ETIM

ETIM 5.0	EC000237
ETIM 6.0	EC000237
ETIM 7.0	EC000237

## Cable - CAB-DSUB37F/RA/OE/22/S/ 3M - 2906396

### Classifications

#### UNSPSC

UNSPSC 13.2	26121620
-------------	----------

### Accessories

#### Accessories

#### Marker carrier cable

Cable marker carrier - KME - 0807083



Cable marker carrier, white, unlabeled, mounting type: Assembly with cable binders, cable diameter: > 5 mm, lettering field size: 20 mm x 8 mm