

Active module - UM-D37M/16R-240AC/DI/C3/L - 2906909

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



VARIOFACE 16-channel module enhances the capabilities of Honeywell Experion LX digital input IOTA's, enabling the use of (240 V AC) digital input signals with (24 V DC) Experion LX systems

Why buy this product

- UM-PRO housing
- DIN rail mounting, includes grounding foot
- Designed to be mounted in the left side of the cabinet
- Per channel LED (coil) signal indication
- Per channel pluggable N/O relay
- Provides isolation between 240 V field devices and 24 V controller



Key Commercial Data

| | |
|--------------------------------------|---------------|
| Packing unit | 1 STK |
| GTIN | |
| GTIN | 4055626163468 |
| Weight per Piece (excluding packing) | 600.000 g |
| Custom tariff number | 85369010 |
| Country of origin | United States |

Technical data

Note

| | |
|-------------------------|---|
| Utilization restriction | EMC: class A product, see manufacturer's declaration in the download area |
|-------------------------|---|

Dimensions

| | |
|-------|--------|
| Width | 184 mm |
|-------|--------|

Active module - UM-D37M/16R-240AC/DI/C3/L - 2906909

Technical data

Dimensions

| | |
|--------|----------|
| Height | 142.3 mm |
| Depth | 65.2 mm |

Ambient conditions

| | |
|---|------------------|
| Ambient temperature (operation) | -40 °C ... 60 °C |
| Ambient temperature (storage/transport) | -40 °C ... 70 °C |

Input data

| | |
|---|---------------------|
| Nominal input voltage U_N | 240 V AC |
| Input voltage range in reference to U_N | 0.8 ... 1.1 |
| Typical input current at U_N | 3 mA |
| Typical response time | 7 ms |
| Typical release time | 15 ms |
| Type of protection | Free-wheeling diode |
| Protective circuit/component | Damping diode |
| Status display/channel | Yellow LED |

Output data

| | |
|-----------------------------|--------------------------------|
| Contact type | 1 N/O contact (double contact) |
| Contact material | AgNi, 5 µm hard gold-plated |
| Maximum switching voltage | 30 V AC 36 V DC |
| Minimum switching voltage | 100 mV |
| Limiting continuous current | 50 mA |
| Min. switching current | 1 mA |

General

| | |
|-------------------------|------------------------|
| No. of channels | 16 |
| With components | yes |
| Mechanical service life | 2×10^7 cycles |
| Operating mode | 100% operating factor |
| Color | yellow |

Connection data for connection 1

| | |
|----------------------------------|---|
| Connection name | Field level |
| Connection method | Screw connection |
| Stripping length | 8 mm |
| Screw thread | M3 |
| Conductor cross section solid | 0.2 mm ² ... 4 mm ² |
| Conductor cross section flexible | 0.2 mm ² ... 2.5 mm ² |

Active module - UM-D37M/16R-240AC/DI/C3/L - 2906909

Technical data

Connection data for connection 1

| | |
|-----------------------------|-----------|
| Conductor cross section AWG | 24 ... 12 |
|-----------------------------|-----------|

Connection data for connection 2


| | |
|-----------------------|------------------|
| Connection name | Controller level |
| Connection method | D-SUB connector |
| Number of connections | 1 |
| Number of positions | 37 |

Supported controller


| | |
|------------------------|--------------------------------|
| Corresponding control | Honeywell Experion LX Series 8 |
| Corresponding I/O card | TDILA1 |
| | TDILB1 |

Drawings

Dimensional drawing



Circuit diagram



Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.0 | 27250313 |
| eCl@ss 4.1 | 27250313 |
| eCl@ss 5.0 | 27250313 |
| eCl@ss 5.1 | 27250313 |
| eCl@ss 7.0 | 27141152 |
| eCl@ss 8.0 | 27141152 |
| eCl@ss 9.0 | 27141152 |

ETIM

| | |
|----------|----------|
| ETIM 4.0 | EC002780 |
|----------|----------|

Active module - UM-D37M/16R-240AC/DI/C3/L - 2906909

Classifications

ETIM

| | |
|----------|----------|
| ETIM 5.0 | EC002780 |
| ETIM 6.0 | EC002780 |

UNSPSC

| | |
|-------------|----------|
| UNSPSC 13.2 | 39121432 |
|-------------|----------|

Accessories

Accessories

System cable

Cable - CABLE-D37SUB/B/B/ 100/KONFEK/S - 2305509



Assembled shielded round cable with 1 x D-SUB socket strip (37-position) on 1 x D-SUB socket strip (37-position), Cable length: 1 m

Cable - CABLE-D37SUB/B/B/ 200/KONFEK/S - 2305512



Assembled shielded round cable with 1 x D-SUB socket strip (37-position) on 1 x D-SUB socket strip (37-position), Cable length: 2 m

Cable - CABLE-D37SUB/B/B/ 300/KONFEK/S - 2305525



Assembled shielded round cable with 1 x D-SUB socket strip (37-position) on 1 x D-SUB socket strip (37-position), Cable length: 3 m

Cable - CABLE-D37SUB/B/B/ 400/KONFEK/S - 2900759



Assembled shielded round cable with 1 x D-SUB socket strip (37-position) on 1 x D-SUB socket strip (37-position), Cable length: 4 m

Active module - UM-D37M/16R-240AC/DI/C3/L - 2906909

Accessories

Cable - CABLE-D37SUB/B/B/ 600/KONFEK/S - 2900760



Assembled shielded round cable with 1 x D-SUB socket strip (37-position) on 1 x D-SUB socket strip (37-position), Cable length: 6 m

Cable - CABLE-D37SUB/B/B/ 800/KONFEK/S - 2900761



Assembled shielded round cable with 1 x D-SUB socket strip (37-position) on 1 x D-SUB socket strip (37-position), Cable length: 8 m

Cable - CABLE-D37SUB/B/B/1000/KONFEK/S - 2900762



Assembled shielded round cable with 1 x D-SUB socket strip (37-position) on 1 x D-SUB socket strip (37-position), Cable length: 10 m

Cable - CABLE-D37SUB/B/B/1500/KONFEK/S - 2900763



Assembled shielded round cable with 1 x D-SUB socket strip (37-position) on 1 x D-SUB socket strip (37-position), Cable length: 15 m

Cable - CABLE-D37SUB/B/B/2000/KONFEK/S - 2900764



Assembled shielded round cable with 1 x D-SUB socket strip (37-position) on 1 x D-SUB socket strip (37-position), Cable length: 20 m

Necessary add-on products

Active module - UM-D37M/16R-240AC/DI/C3/L - 2906909

Accessories

Front adapters - FLKM-PA-D37/HW/DIO/C300 - 2901423



VARIOFACE front adapter, for Honeywell C300, Series C I/O, maximum of 1 x 16 channels can be connected (37-pos. D-SUB connector). Specifically for connecting digital, redundant I/O cards.

Spare parts

Single relay - REL-MR- 60DC/21AU - 2961134



Plug-in miniature power relay, with multi-layer gold contact, 1 PDT, input voltage 60 V DC