

Cable - CAB-DSUB25M/OE/22/TP/S/ 5M - 2909608

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Assembled shielded round cable; connection 1: Twisted pair (25-position) (The wires are marked and fitted with ferrules.); connection 2: D-SUB pin strip (1x 25-position); cable length: 5 m

Your advantages

- Individual wire marking: 1, 2, 3, 4, etc.
- Twisted pairs fitted with ferrules
- Screw connection: 2 UNC 4-40 screws
- Open end at one end
- D-SUB socket or pin strip at one end

Key Commercial Data

Packing unit	1 pc
GTIN	 4 055626 682136
GTIN	4055626682136
Weight per Piece (excluding packing)	750.000 g
Custom tariff number	85444290
Country of origin	United States

Technical data

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

General

Max. permissible operating voltage	125 V AC
------------------------------------	----------

Cable - CAB-DSUB25M/OE/22/TP/S/ 5M - 2909608

Technical data

General

	125 V DC
Max. current carrying capacity per path	1 A
Length of cable	5 m
External cable diameter	11.62 mm
Single wire, cross section	0.36 mm ²
Single wire, cross section [AWG]	22
Shielding	yes
	Overall foil shield

Connection data

Connection name	Field level
Connection method	D-SUB pin strip
Number of connections	1
Number of positions	25

Connection data 2

Connection name	Controller level
Connection method	Twisted pair
Number of positions	25
Note	The wires are marked and fitted with ferrules.

Supported controller

Classifications

eCl@ss

eCl@ss 5.0	27242200
eCl@ss 5.1	27242200
eCl@ss 6.0	27249200
eCl@ss 7.0	27249205
eCl@ss 8.0	27249205
eCl@ss 9.0	27242220

ETIM

ETIM 5.0	EC000237
ETIM 6.0	EC000237
ETIM 7.0	EC000237

Cable - CAB-DSUB25M/OE/22/TP/S/ 5M - 2909608

Accessories

Accessories

Marker carrier cable

Cable marker carrier - KME - 0807083



Cable marker carrier, white, unlabeled, mounting type: Assembly with cable binders, cable diameter: > 5 mm, lettering field size: 20 mm x 8 mm