

Cable - CAB-TE MR24F/OE/24/S/ 1M - 2909746

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Migration cable for Bailey NET90/Infi90 to modern control platforms. Open-end cable for universal configurations, 24 conductors, 1.0 m

Your advantages

- Individual wire marking: 1, 2, 3, 4, etc.
- Individual wires fitted with ferrules
- Screw connection: 2 UNC 4-40 screws
- Open end at one end
- D-SUB socket or pin strip at one end
- 1:1 connection

Key Commercial Data

Packing unit	1 pc
GTIN	 4 055626 682624
GTIN	4055626682624
Weight per Piece (excluding packing)	200.000 g
Custom tariff number	85444290
Country of origin	United States

Technical data

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

General

Max. permissible operating voltage	125 V AC
	125 V DC
Max. current carrying capacity per path	1 A
Length of cable	1 m

Cable - CAB-TE MR24F/OE/24/S/ 1M - 2909746

Technical data

General

External cable diameter	9.4 mm
Single wire, cross section	0.25 mm ²
Single wire, cross section [AWG]	24
Shielding	yes
	Overall foil and braid shield

Supported controller

Controller	universal
------------	-----------

Color code

Connector 1 = connector 2 (optional) = wire color	MR24F (1) = black
	MR24F (2) = white
	MR24F (3) = red
	MR24F (4) = green
	MR24F (5) = orange
	MR24F (6) = blue
	MR24F (7) = white-black
	MR24F (8) = red-black
	MR24F (9) = green-black
	MR24F (10) = orange-black
	MR24F (11) = blue-black
	MR24F (12) = black-white
	MR24F (13) = red-white
	MR24F (14) = green-white
	MR24F (15) = blue-white
	MR24F (16) = black-red
	MR24F (17) = white-red
	MR24F (18) = orange-red
	MR24F (19) = blue-red
	MR24F (20) = red-green
	MR24F (21) = orange-green
	MR24F (22) = black-white-red
	MR24F (23) = white-black-red
	MR24F (24) = red-black-white

Cable - CAB-TE MR24F/OE/24/S/ 1M - 2909746

Classifications

eCl@ss

eCl@ss 5.1	27242200
eCl@ss 6.0	27249200
eCl@ss 7.0	27249205
eCl@ss 8.0	27249205
eCl@ss 9.0	27242220

ETIM

ETIM 5.0	EC000237
ETIM 6.0	EC000237
ETIM 7.0	EC000237

Accessories

Accessories

Marker carrier cable

Cable marker carrier - KME - 0807083



Cable marker carrier, white, unlabeled, mounting type: Assembly with cable binders, cable diameter: > 5 mm, lettering field size: 20 mm x 8 mm