

## Single plug-in bridge - PLC-BP A1-14 - 2980283

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Passive feed-through bridge; can be plugged in instead of a relay or a solid-state relay, bridges terminal points A1 and 14



COMPLETE™

### Key Commercial Data

Packing unit	1 pc
Minimum order quantity	10 pc
GTIN	 4 017918 729981
GTIN	4017918729981
Weight per Piece (excluding packing)	4.810 g
Custom tariff number	85389099
Country of origin	Germany

### Technical data

#### Dimensions

Width	5 mm
Height	28 mm
Depth	15 mm

#### General

Nominal voltage $U_N$	60 V AC/DC
Color	black

#### Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50
------------	--

# Single plug-in bridge - PLC-BP A1-14 - 2980283

## Technical data

### Environmental Product Compliance

	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"
--	---

## Classifications

### eCl@ss

eCl@ss 4.0	27371100
eCl@ss 4.1	27371100
eCl@ss 5.0	27371600
eCl@ss 5.1	27371600
eCl@ss 6.0	27379200
eCl@ss 7.0	27379208
eCl@ss 8.0	27379208
eCl@ss 9.0	27371692

### ETIM

ETIM 4.0	EC002586
ETIM 5.0	EC002586
ETIM 6.0	EC002586
ETIM 7.0	EC002586

### UNSPSC

UNSPSC 6.01	30211802
UNSPSC 7.0901	39121402
UNSPSC 11	39121402
UNSPSC 12.01	39121402
UNSPSC 13.2	39121426

## Approvals

### Approvals

---

Approvals

PRS / GL

---

Ex Approvals

---

## Single plug-in bridge - PLC-BP A1-14 - 2980283

### Approvals

#### Approval details

PRS		<a href="http://www.prs.pl/">http://www.prs.pl/</a>	TE/2109/880590/16
-----	---	---	-------------------

GL		<a href="https://approvalfinder.dnvgl.com/">https://approvalfinder.dnvgl.com/</a>	46016-03 HH
----	---	---	-------------