


End cover - D-UK3D-MSTBV-5,08 - 3002186

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

End cover, pitch: 5.08 mm, length: 60 mm, width: 2 mm, height: 49.5 mm, number of positions: 1, color: gray



Key Commercial Data

Packing unit	1 pc
Minimum order quantity	50 pc
GTIN	 4 017918 090197
GTIN	4017918090197
Weight per Piece (excluding packing)	4.244 g
Custom tariff number	85389099
Country of origin	Germany

Technical data

General

Number of positions	1
Color	gray
Material	PA
Flammability rating according to UL 94	V2

Dimensions

Width	2 mm
Length	60 mm
Height	49.5 mm
Pitch	5.08 mm

End cover - D-UK3D-MSTBV-5,08 - 3002186

Technical data

Standards and Regulations

Flammability rating according to UL 94	V2
--	----

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 4.0	21011300
eCl@ss 4.1	27260700
eCl@ss 5.0	27141100
eCl@ss 5.1	27260700
eCl@ss 6.0	27141100
eCl@ss 7.0	27141133
eCl@ss 8.0	27141133
eCl@ss 9.0	27141133

ETIM

ETIM 2.0	EC000897
ETIM 3.0	EC000897
ETIM 4.0	EC000886
ETIM 5.0	EC000886
ETIM 6.0	EC000886
ETIM 7.0	EC000886

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121425