

Insertion bridge - EB 80-12 - 3009338

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Insertion bridge, Number of positions: 80, Color: gray

The figure shows a version of the article

Key Commercial Data

Packing unit	1 pc
GTIN	 4 017918 091781
Weight per Piece (excluding packing)	150.0 g
Custom tariff number	85389099
Country of origin	Germany

Technical data

Technical data

Color	gray
Material	Copper
Number of positions	80
Pitch	12.00 mm
Flammability rating according to UL 94	V2

Standards and Regulations

Flammability rating according to UL 94	V2
----------------------------------------	----

Classifications

eCl@ss

eCl@ss 4.0	27141199
eCl@ss 4.1	27141199
eCl@ss 5.0	27141140

Insertion bridge - EB 80-12 - 3009338

Classifications

eCl@ss

eCl@ss 5.1	27141140
eCl@ss 6.0	27141140
eCl@ss 7.0	27141140
eCl@ss 8.0	27141140

ETIM

ETIM 2.0	EC000489
ETIM 3.0	EC000489
ETIM 4.0	EC000489
ETIM 5.0	EC000489

UNSPSC

UNSPSC 6.01	30211829
UNSPSC 7.0901	39121426
UNSPSC 11	39121426
UNSPSC 12.01	39121426
UNSPSC 13.2	39121426

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approvals submitted

Approval details

EAC
