

Latching - UPRZ - 3045570

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Latching, length: 39.8 mm, width: 10 mm, number of positions: 2, color: orange

Your advantages

- Can be snapped into the plug housing as an option
- The conductor can be fixed using Phoenix Contact cable binders
- Latching and strain relief in one component



COMPLIANT

Key Commercial Data

Packing unit	1 pc
Minimum order quantity	50 pc
GTIN	 4 046356 055772
GTIN	4046356055772
Weight per Piece (excluding packing)	1.540 g
Custom tariff number	85389099
Country of origin	Poland

Technical data

General

Number of positions	2
Color	orange
Material	PA-GF
Flammability rating according to UL 94	V2

Dimensions

Latching - UPRZ - 3045570

Technical data

Dimensions

Width	10 mm
Length	39.8 mm

Standards and Regulations

Flammability rating according to UL 94	V2
--	----

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 10.0.1	27141190
eCl@ss 4.0	27141100
eCl@ss 4.1	27141100
eCl@ss 5.0	27141100
eCl@ss 5.1	27141100
eCl@ss 6.0	27141100
eCl@ss 7.0	27141190
eCl@ss 8.0	27141190
eCl@ss 9.0	27141190

ETIM

ETIM 2.0	EC000897
ETIM 3.0	EC000897
ETIM 4.0	EC002498
ETIM 5.0	EC002848
ETIM 6.0	EC002848
ETIM 7.0	EC002848

UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121411
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	39121410

Latching - UPRZ - 3045570

Approvals


Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		EAC-Zulassung
-----	---	---------------
