

Fuse plug - P-FU 6,3X32-EX - 3046499

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Fuse plug, fuse type: Sand filled, connection method: Plug connection, nominal current: 10 A, nom. voltage: 500 V, width: 8.2 mm, fuse type: G / 6,3 x 32, color: black

Your advantages

- Large-surface labeling option
- Test contacts on both sides of the fuse
- Test contacts on both sides of the fuse
- Versions with bipolar error display
- Can be used for overload/short-circuit protection



Key Commercial Data

Packing unit	1 pc
Minimum order quantity	50 pc
GTIN	 4 046356 919258
GTIN	4046356919258
Weight per Piece (excluding packing)	6.000 g
Custom tariff number	85369095
Country of origin	Poland

Technical data

General

Note	Prior to replacing the cartridge fuse, disconnect the fuse connector from the basic terminal block.
Number of levels	1
Color	black

Fuse plug - P-FU 6,3X32-EX - 3046499

Technical data

General

Insulating material	PA
Flammability rating according to UL 94	V0
Area of application	Machine building Plant engineering

Dimensions

Width	8.2 mm
Length	40 mm

General

Fuse	G / 6,3 x 32
Fuse type	Sand filled
Degree of pollution	3
Maximum power dissipation	1.6 W (Short-circuit and overload protection)
Maximum load current	10 A (the current is determined by the fuse used)
Nominal current I _N	10 A (the current is determined by the fuse used)
Nominal voltage U _N	500 V (if used as fuse terminal block) 500 V (if used as disconnect terminal block)
Open side panel	No

Connection data

Connection method	Plug connection
-------------------	-----------------

Standards and Regulations

Flammability rating according to UL 94	V0
--	----

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e No hazardous substances above threshold values
------------	---

Classifications

eCl@ss

eCl@ss 4.0	27141100
eCl@ss 4.1	27141100
eCl@ss 5.0	27141100
eCl@ss 5.1	27141100
eCl@ss 6.0	27141100
eCl@ss 7.0	27141149
eCl@ss 8.0	27141149

Fuse plug - P-FU 6,3X32-EX - 3046499

Classifications

eCl@ss

eCl@ss 9.0	27141149
------------	----------

ETIM

ETIM 2.0	EC000897
ETIM 3.0	EC000897
ETIM 4.0	EC000899
ETIM 5.0	EC002018
ETIM 6.0	EC002018
ETIM 7.0	EC002018

UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	39121409

Approvals

Approvals

Approvals

EAC

Ex Approvals

IECEX / ATEX / UL Recognized / cUL Recognized / cULus Recognized

Approval details

EAC		RU C- DE.A*30.B.01742
-----	--	--------------------------