

# Connection element - HV M12/1-VS 2 - 3049631


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Connection element, length: 62 mm, width: 25 mm, height: 4 mm, number of positions: 2, color: silver



## Key Commercial Data

Packing unit	10 STK
GTIN	 4 046356 313520
GTIN	4046356313520

## Technical data

### Technical data

Color	silver
Material	Copper
Number of positions	2
Length	62 mm
Height	4 mm
Width	25 mm
Hole diameter	12.6 mm
Drill hole spacing	34 mm
Maximum load current	269 A

## Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Phoenix Contact 2018 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>