

Cover profile - FBP-3/14 TR - 3069925

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cover profile, can optionally be sealed, Length: 147 mm, Width: 74.1 mm, Height: 32 mm, Color: transparent

The figure shows a version of the article

Key Commercial Data

Packing unit	1 STK
GTIN	 4 055626 137421
GTIN	4055626137421
Weight per Piece (excluding packing)	60.000 g
Custom tariff number	39162000
Country of origin	Poland

Technical data

General

Color	transparent
Insulating material	PVC
Flammability rating according to UL 94	V0
Overvoltage category	III
Insulating material group	I
Ambient temperature (operation)	-15 °C ... 65 °C

Dimensions

Width	74.1 mm
Length	147 mm

Cover profile - FBP-3/14 TR - 3069925

Technical data

Dimensions

Height	32 mm
--------	-------

Standards and Regulations

Flammability rating according to UL 94	V0
--	----

Classifications

eCl@ss

eCl@ss 4.0	27110804
eCl@ss 4.1	27110804
eCl@ss 5.0	27141143
eCl@ss 5.1	27141143
eCl@ss 6.0	27379200
eCl@ss 7.0	27141143
eCl@ss 8.0	27141190
eCl@ss 9.0	27141190

ETIM

ETIM 3.0	EC000012
ETIM 4.0	EC000886
ETIM 5.0	EC002848
ETIM 6.0	EC002848

UNSPSC

UNSPSC 6.01	30212109
UNSPSC 7.0901	39121708
UNSPSC 11	39121708
UNSPSC 12.01	39121708
UNSPSC 13.2	39121410