

Plug-in bridge - FBS 3-3,5 GY - 3213167

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Plug-in bridge, pitch: 3.5 mm, number of positions: 3, color: gray

Your advantages

- The 2- to 50-pos. jumpers can bridge up to 50 terminal blocks in the two bridge shafts of the CLIPLINE complete system in one step

COMPLETE RoHS

Key Commercial Data

| | |
|--------------------------------------|---|
| Packing unit | 1 pc |
| Minimum order quantity | 50 pc |
| GTIN |  4 046356 594417 |
| GTIN | 4046356594417 |
| Weight per Piece (excluding packing) | 1.200 g |
| Custom tariff number | 85366990 |
| Country of origin | Germany |

Technical data

Technical data

| | |
|--|---|
| Color | gray |
| Material | Copper |
| Number of positions | 3 |
| Pitch | 3.5 mm |
| Flammability rating according to UL 94 | V0 |
| Maximum load current | 17.5 A (The current values for the jumpers can deviate when used in different modular terminal blocks. The precise values can be found in the accessories data for the respective modular terminal blocks.) |

Plug-in bridge - FBS 3-3,5 GY - 3213167

Technical data

Standards and Regulations

| | |
|--|----|
| Flammability rating according to UL 94 | V0 |
|--|----|

Environmental Product Compliance

| | |
|------------|---|
| China RoHS | Environmentally friendly use period: unlimited = EFUP-e |
| | No hazardous substances above threshold values |

Classifications

eCl@ss

| | |
|---------------|----------|
| eCl@ss 10.0.1 | 27141140 |
| eCl@ss 4.0 | 21011300 |
| eCl@ss 4.1 | 27141100 |
| eCl@ss 5.0 | 27141100 |
| eCl@ss 5.1 | 27141100 |
| eCl@ss 6.0 | 27141100 |
| eCl@ss 7.0 | 27141140 |
| eCl@ss 8.0 | 27141140 |
| eCl@ss 9.0 | 27141140 |

ETIM

| | |
|----------|----------|
| ETIM 4.0 | EC000489 |
| ETIM 5.0 | EC000489 |
| ETIM 6.0 | EC000489 |
| ETIM 7.0 | EC000489 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 30211829 |
| UNSPSC 7.0901 | 39121426 |
| UNSPSC 11 | 39121426 |
| UNSPSC 12.01 | 39121426 |
| UNSPSC 13.2 | 39121426 |
| UNSPSC 18.0 | 39121426 |
| UNSPSC 19.0 | 39121426 |
| UNSPSC 20.0 | 39121426 |
| UNSPSC 21.0 | 39121426 |

Approvals

Approvals

Plug-in bridge - FBS 3-3,5 GY - 3213167

Approvals

Approvals

EAC / EAC

Ex Approvals

Approval details

| | | |
|-----|---|---------------|
| EAC |  | EAC-Zulassung |
|-----|---|---------------|

| | | |
|-----|---|--------------------------|
| EAC |  | RU C- DE.A*30.B.01742 |
|-----|---|--------------------------|

Accessories

Accessories

Cutting tools

Front cutter - CUTFOX-FBS - 1212124



Cutting tool, for separating individual jumper bars from FBS ... plug-in bridges and EB ... insertion bridges
