

## Ring cable lug - C-RC 10/M10 DIN - 3240092

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Ring cable lug, non-insulated, 10 mm<sup>2</sup>, M10

### Why buy this product

- ✓ The CRIMPFOX-RC... tools from our CRIMPFOX range of crimping pliers are available for optimum crimping
- ✓ The hard-soldered press zone enables maximum conductor pull-out values to be achieved
- ✓ The ring cable lugs without plastic sleeve are made from high-quality tin-plated electrolytic copper for maximum protection against corrosion



### Key Commercial Data

Packing unit	1 STK
Minimum order quantity	100 STK
Weight per Piece (excluding packing)	3.800 g
Custom tariff number	85369010
Country of origin	China

### Technical data

#### Dimensions

Length (b)	30 mm
Width (a)	18 mm
Maximum stripping length	11 mm
Length of insulation sleeve (c)	8 mm
Inner dimension of the insulating collar (d)	4.5 mm
Distance between the center and the insulation sleeve (e)	13 mm
Inner diameter (f)	10.5 mm
Material thickness (g)	1.1 mm

#### Ambient conditions

# Ring cable lug - C-RC 10/M10 DIN - 3240092

## Technical data

### Ambient conditions


Ambient temperature (operation)	110 °C
---------------------------------	--------

### General

Color	silver
Stripping length	11 mm
Material	Copper
Coating	Tin-plated

## Drawings

Dimensional drawing



## Approvals

### Approvals

Approvals

EAC / EAC

Ex Approvals

### Approval details

EAC 7500651.22.01.00246
-------------------------

EAC EAC-Zulassung
-------------------