

## Ring cable lug - C-RC 120/M16 DIN - 3240127


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Ring cable lug, non-insulated, 120 mm<sup>2</sup>, M16



### Key Commercial Data

Packing unit	1 pc
Minimum order quantity	25 pc
GTIN	 4 046356 453448
GTIN	4046356453448
Weight per Piece (excluding packing)	59.200 g
Custom tariff number	85369010
Country of origin	China

### Technical data

#### Dimensions

Length (b)	62 mm
Width (a)	28 mm
Maximum stripping length	25 mm
Length of insulation sleeve (c)	22 mm
Inner dimension of the insulating collar (d)	16.5 mm
Distance between the center and the insulation sleeve (e)	26 mm
Inner diameter (f)	17 mm
Material thickness (g)	3 mm

#### Ambient conditions

Ambient temperature (operation)	110 °C
---------------------------------	--------

# Ring cable lug - C-RC 120/M16 DIN - 3240127

## Technical data

### General

Color	silver
Stripping length	25 mm
Material	Copper
Coating	tin-plated

### Standards and Regulations

Design according to standard	DIN 46234
------------------------------	-----------

### Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

## Classifications

### eCl@ss

eCl@ss 5.1	27400200
eCl@ss 6.0	27400200
eCl@ss 7.0	27400203
eCl@ss 8.0	27400204
eCl@ss 9.0	27400204

### ETIM

ETIM 2.0	EC000005
ETIM 3.0	EC000005
ETIM 4.0	EC001052
ETIM 5.0	EC001052
ETIM 6.0	EC001052
ETIM 7.0	EC001052

### UNSPSC

UNSPSC 6.01	30211923
UNSPSC 7.0901	27121703
UNSPSC 11	27121703
UNSPSC 12.01	27121703
UNSPSC 13.2	27121707

## Approvals

### Approvals

## Ring cable lug - C-RC 120/M16 DIN - 3240127

### Approvals

Approvals

EAC

---

Ex Approvals

---

### Approval details

EAC		EAC-Zulassung
-----	---	---------------

---