

DIN rail perforated - NS 30/15 PERF.2000MM - 3240262

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



DIN rail perforated, C profile, width: 30 mm, height: 15 mm, similar to EN 60715, material: Steel, galvanized, length: 2000 mm

Your advantages

- ✓ Individual or bundled cables with a diameter of up to 64 mm can be installed safely and easily
- ✓ The halogen-free plastic troughs have been designed to be perfectly secure while simultaneously protecting the conductors
- ✓ The cable clamps provide strain relief

Key Commercial Data

Packing unit	2 M
Minimum order quantity	5 M
GTIN	 4 046356 480833
GTIN	4046356480833
Custom tariff number	72166190
Country of origin	Germany

Technical data

Dimensions

Height	15 mm
Length	2000 mm
Width	30 mm
Hole width	15.00 mm
Hole height	6.20 mm
Drill hole spacing	25.00 mm

DIN rail perforated - NS 30/15 PERF.2000MM - 3240262

Technical data

General

Material	Steel
Coating	galvanized

Standards and Regulations

Test standard	similar to EN 60715
---------------	---------------------

Classifications

eCl@ss

eCl@ss 5.1	27141100
eCl@ss 6.0	27141100
eCl@ss 7.0	27141143
eCl@ss 8.0	27141143
eCl@ss 9.0	27400602

ETIM

ETIM 2.0	EC001285
ETIM 3.0	EC001285
ETIM 4.0	EC000212
ETIM 5.0	EC001285
ETIM 6.0	EC001285
ETIM 7.0	EC001285

UNSPSC

UNSPSC 6.01	30212109
UNSPSC 7.0901	39121708
UNSPSC 11	39121708
UNSPSC 12.01	39121708
UNSPSC 13.2	39121708