

Cover profile - CD COVER 30 BU - 3240331


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cover for cable duct, blue, width: 30 mm, length: 2000 mm



Key Commercial Data

Packing unit	1 pc
Minimum order quantity	10 pc
GTIN	 4 046356 508117
GTIN	4046356508117
Custom tariff number	39259020
Country of origin	Germany

Technical data

Dimensions

Length (b)	2000 mm
Width (a)	30 mm
Height (c)	14.4 mm

Ambient conditions

Ambient temperature (operation)	-5 °C ... 60 °C
---------------------------------	-----------------

General

Color	blue
Components	Lead-free
Flammability rating according to UL 94	V0
Material	PVC

Cover profile - CD COVER 30 BU - 3240331

Technical data

Standards and Regulations

Flammability rating according to UL 94	V0
--	----

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 4.0	27140600
eCl@ss 4.1	27140600
eCl@ss 5.0	27140600
eCl@ss 5.1	27140600
eCl@ss 6.0	27400700
eCl@ss 7.0	27400776
eCl@ss 8.0	27400776
eCl@ss 9.0	27400776

ETIM

ETIM 2.0	EC000012
ETIM 3.0	EC000727
ETIM 4.0	EC000727
ETIM 5.0	EC000727
ETIM 6.0	EC000727
ETIM 7.0	EC000727

UNSPSC

UNSPSC 6.01	30101815
UNSPSC 7.0901	30101815
UNSPSC 11	30101815
UNSPSC 12.01	30101815
UNSPSC 13.2	39131712