

Connector - C-SCFMI 2,5/6,3X0,8 - 3240530

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Flat plug distributor, isolated, blue, 1.5 - 2.5 mm², for plug and sleeve 6.3 x 0.8 mm

Product Features

- Hard-soldered crimping zone for maximum conductor pull-out forces in connection with CRIMPFOX RCI... pliers
- Easy and reliable conductor entry thanks to 'EASY ENTRY'
- Halogen-free
- Electrolytically tin-plated



Key Commercial Data

Packing unit	1 pc
Minimum order quantity	50 pc
Weight per Piece (excluding packing)	1.6 g
Custom tariff number	85369010
Country of origin	China

Technical data

Dimensions

Length (b)	23 mm
Width (a)	6.3 mm
Length of insulation sleeve (c)	11 mm
Inner dimension of the insulating collar (d)	11 mm
Material thickness (g)	0.4 mm

Ambient conditions

Ambient temperature (operation)	-20 °C ... 105 °C
Short-term temperature	120 °C
Max. permanent temperature	105 °C

Connector - C-SCFMI 2,5/6,3X0,8 - 3240530

Technical data

General

Color	blue
Stripping length	8 mm
Components	Halogen-free
Material	Brass
Insulating material	PA
Coating	electrogalvanized

Classifications

eCl@ss

eCl@ss 4.0	27140815
eCl@ss 4.1	27140815
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27400209
eCl@ss 7.0	27440304

ETIM

ETIM 2.0	EC000516
ETIM 3.0	EC000516
ETIM 4.0	EC000516
ETIM 5.0	EC000516

UNSPSC

UNSPSC 6.01	30211923
UNSPSC 7.0901	39121522
UNSPSC 11	39121522
UNSPSC 12.01	39121522
UNSPSC 13.2	39121522

Approvals

Approvals

Approvals

EAC / EAC

Connector - C-SCFMI 2,5/6,3X0,8 - 3240530

Approvals

Ex Approvals

Approvals submitted

Approval details

EAC

EAC

Drawings

Dimensional drawing

