

## Protective hose - WP-STEEL S 10 - 3240686

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Protective hose in stainless steel

### Key Commercial Data

Packing unit	1 M
Minimum order quantity	10 M
Weight per Piece (excluding packing)	96.0 g
Custom tariff number	83071000
Country of origin	Germany

### Technical data

#### Dimensions

Inner diameter (f)	8.00 mm
Outside diameter	10.00 mm

#### Ambient conditions

Ambient temperature (operation)	-200 °C ... 600 °C
---------------------------------	--------------------

#### General

Color	silver
Type	Spirals
Components	Halogen-free
Material	Stainless steel 1.4301/AISI 304
Bending radius, static	22.00 mm

### Classifications

#### eCl@ss

eCl@ss 4.0	27141131
eCl@ss 4.1	27141131

## Protective hose - WP-STEEL S 10 - 3240686

### Classifications

#### eCl@ss

eCl@ss 5.0	27141131
eCl@ss 5.1	27141120
eCl@ss 6.0	27141120
eCl@ss 7.0	27141120
eCl@ss 8.0	27430301

#### ETIM

ETIM 3.0	EC000897
ETIM 4.0	EC001179
ETIM 5.0	EC001179

#### UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	39121411