

Protective hose - WP-STEEL PVC C 36 - 3240872


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Galvanized steel protective hose with PVC coating



Key Commercial Data

Packing unit	1 M
Minimum order quantity	10 M
GTIN	 4 046356 737371
GTIN	4046356737371
Custom tariff number	83071000
Country of origin	Germany

Technical data

Dimensions

Inner diameter (f)	29 mm
Outside diameter	36 mm

Ambient conditions

Ambient temperature (operation)	-25 °C ... 80 °C
Short-term temperature	100 °C
Degree of protection	IP68

General

Color	black
Type	Spirals, sheathed
Material	Steel, galvanized/PVC

Protective hose - WP-STEEL PVC C 36 - 3240872

Technical data

General

Bending radius, static	90 mm
Bending radius, dynamic	225 mm
Tensile strength	500 N

Standards and Regulations

Halogen-free	no
--------------	----

Classifications

eCl@ss

eCl@ss 10.0.1	27430301
eCl@ss 4.0	27140900
eCl@ss 4.1	27140900
eCl@ss 5.0	27140900
eCl@ss 5.1	27140900
eCl@ss 6.0	27140900
eCl@ss 7.0	27430301
eCl@ss 8.0	27430301
eCl@ss 9.0	27430301

ETIM

ETIM 3.0	EC000897
ETIM 4.0	EC001179
ETIM 5.0	EC001179
ETIM 6.0	EC001179
ETIM 7.0	EC001179

UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	40141734
UNSPSC 18.0	40141734
UNSPSC 19.0	40141734
UNSPSC 20.0	40141734
UNSPSC 21.0	40141734

Protective hose - WP-STEEL PVC C 36 - 3240872

Approvals

Approvals

Approvals

VDE Zeichengenehmigung

Ex Approvals

Approval details

VDE Zeichengenehmigung



<http://www2.vde.com/de/Institut/Online-Service/VDE-gepruefteProdukte/Seiten/Online-Suche.aspx>

Accessories

Accessories

Corrugated pipe screw connection

Screw connection - WP-G BRASS IP65 PG29 - 3241056



Cable gland made from brass with Pg thread, IP65 protection

Screw connection - WP-G BRASS IP65 M32 - 3241063



Cable gland made from brass with metric thread, IP65 protection

Mounting material

Protective hose - WP-STEEL PVC C 36 - 3240872

Accessories

Hose clamp - WP-BASE HF 37 - 3240972



Hose clamps

Protective hose fixing bracket - WP-BASE A PG29 - 3241081



Fixing bracket for protective sleeves, fixed with two screws

Protective cap

Cable protection end sleeve - WP-SC BRASS WP PVC 36 - 3241077



End sleeves as cable protection, made of brass, for WP-STEEL PVC C
