

Screw connection - WP-G HF IP69K M10 BK - 3240881


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cable gland, metric thread, IP68/69k protection, straight

RoHS

Key Commercial Data

Packing unit	1 pc
Minimum order quantity	50 pc
GTIN	 4 046356 709880
GTIN	4046356709880
Weight per Piece (excluding packing)	4.000 g
Custom tariff number	39174000
Country of origin	Germany

Technical data

Dimensions

Width (a)	17 mm
Height (c)	34.5 mm
Wrench size	16 mm
Outside diameter	10 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
Degree of protection	IP68/IP69K
Resistance to UV radiation	no

General

Screw connection - WP-G HF IP69K M10 BK - 3240881

Technical data

General

Color	black
Type	Outer thread
Components	free from silicone, halogen, and cadmium
Material	PA 6

Standards and Regulations

Resistance to UV radiation	no
Halogen-free	yes
Connection in acc. with standard	UL
Flammability rating according to UL 94	V2

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 10.0.1	27144432
eCl@ss 11.0	27144432
eCl@ss 4.0	27141200
eCl@ss 4.1	27141200
eCl@ss 5.0	27149100
eCl@ss 5.1	27141100
eCl@ss 6.0	27149100
eCl@ss 7.0	27149109
eCl@ss 9.0	27144432

ETIM

ETIM 3.0	EC000897
ETIM 4.0	EC001178
ETIM 6.0	EC000441
ETIM 7.0	EC000441

UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411

Screw connection - WP-G HF IP69K M10 BK - 3240881

Classifications

UNSPSC

UNSPSC 13.2	39121311
UNSPSC 18.0	39121311
UNSPSC 19.0	39121311
UNSPSC 20.0	39121311
UNSPSC 21.0	39121311

Approvals

Approvals

Approvals

LR / UL Recognized / VDE Zeichengenehmigung

Ex Approvals

Approval details

LR		http://www.lr.org/en
----	--	---

UL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm
---------------	--	---

VDE Zeichengenehmigung		http://www2.vde.com/de/Institut/Online-Service/VDE-gepruefteProdukte/Seiten/Online-Suche.aspx
------------------------	--	---

Accessories

Accessories

Corrugated pipe

Screw connection - WP-G HF IP69K M10 BK - 3240881

Accessories

Protective hose - WP-PA HF 10,0 BK - 3240680



Polyamide protective hose, inflammability class V0, UV resistant

Protective hose - WP-PA HF-HB 10,0 BK - 3240838



Polyamide protective hose, inflammability class HB, UV resistant

Seal

Flat gasket - WP-FS IP68 M10 - 3241159



Flat gasket, material: Perbunan, degree of protection: IP68, color: black

Flat gasket - WP-FS HF IP68 M10 - 3241173



Flat gasket, material: Centellen, degree of protection: IP68, color: green
