

Screw connection - WP-G HF IP69K M20 BK - 3240884

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Cable gland, metric thread, IP68/69k protection, straight

The figure shows the WP-G HF IP69K M10 BK version

RoHS

Key Commercial Data

Packing unit	1 STK
Minimum order quantity	50 STK
GTIN	 4 046356 709910
GTIN	4046356709910
Weight per Piece (excluding packing)	11.250 g
Custom tariff number	39174000
Country of origin	Germany

Technical data

Dimensions

Width (a)	29.5 mm
Height	44.5 mm
Wrench size	27.00 mm
Outside diameter	21.20 mm
Cable diameter	21.2 mm ... 21.2 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 115 °C
Degree of protection	IP68/IP69K

Screw connection - WP-G HF IP69K M20 BK - 3240884

Technical data

General

Color	black
Design	Straight
Type	Outer thread
Components	free from silicone, halogen, and cadmium
Flammability rating according to UL 94	V0
Material	PA

Standards and Regulations

Connection in acc. with standard	UL
Flammability rating according to UL 94	V0

Approvals

Approvals


Approvals


UL Recognized / VDE Zeichengenehmigung / LR

Ex Approvals

Approval details

UL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm
---------------	---	---

VDE Zeichengenehmigung		http://www.vde.com/en/Institute/OnlineService/VDE-approved-products/Pages/Online-Search.aspx
------------------------	---	---

LR		http://www.lr.org/en
----	---	---
